



Technical data


NU213EAT2XC3

Single row cylindrical roller bearings


Single row cylindrical roller bearing, floating, separable, polyamide cage

ULTAGE®

VISUAL (S)



NU213EAT2XC3
 Single row cylindrical roller bearings



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	65 mm
D - External diameter	120 mm
B - Bearing/Inner ring width	23 mm
E - Upper roller diameter	108,5 mm
F - Under roller diameter	78,5 mm
d1 - IR flange outer diameter	84,5 mm
rNs - Min fillet radius	1,5 mm
rs - Min fillet radius	1,5 mm
Radial clearance class	C3
Mass	1,21 kg

PRODUCT PERFORMANCE	
C - Dynamic load	127000000 mN

NU213EAT2XC3

Single row cylindrical roller bearings

PRODUCT PERFORMANCE

C0 - Static load	119000000 mN
Cu - Fatigue limit load	14500000 mN
N lim - Oil lubrication limit speed	45600 °/s
N lim - Grease lubrication limit speed	32400 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	73 mm
db min - Min inner ring GO diameter	81 mm
Da max - Max shoulder diameter OR	112 mm
Db min - Small face shoulder min diameter	110 mm
ra max - Max fillet radius	1,5 mm
r1a - Max fillet radius	1,5 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = Fr$$

Equivalent static radial load

$$P_0 = Fr$$



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15