



HelaTape Power - Self-amalgamating Tapes

HelaTape Power 600 - Self-amalgamating Low Voltage Tape

Features and Benefits

- Self-amalgamating low voltage rubber tape
- Primary insulation at not more than 600 volts
- Easily conforms to irregular shapes and surfaces
- Void-free electrically stable layering
- Compatible with all extruded dielectric cable insulations
- Recommended use in conjunction with HelaTape Flex for outer jacketing



HelaTape Power 600 is a self-amalgamating low-voltage rubber tape.

MATERIAL	Natural Rubber (NR)
Operating Temperature	+80 °C
Intermittent Operating Temperature	+95 °C
Tensile Strength	2.40 MPa
Elongation at break	450 %
Volume Resistance	10 ¹³ Ω cm
Dielectric Strength	25 kV/mm

HF ✓

RoHS ✓

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-POWER600	0.76	19.0	6.7 m	Black (BK)	711-00200
	0.76	38.0	6.7 m	Black (BK)	711-00201

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.