

# Product datasheet

Specifications



Head for illuminated push button,  
Harmony XB5, grey bezel, red flush,  
22mm, universal LED, spring return,  
clear boot

ZB5AW543C0

**Important message:** A change in appearance may be noted on the product but does not affect its use in terms of function and safety. This makes it compatible with our Universal LED blocks  
**EAN Code:** 3606489770280

## Main

|                                 |                                  |
|---------------------------------|----------------------------------|
| Range of product                | Harmony XB5                      |
| Product or component type       | Head for illuminated push-button |
| Device short name               | ZB5                              |
| Product compatibility           | Universal LED                    |
| Bezel material                  | Plastic colour plated grey       |
| Mounting diameter               | 22 mm                            |
| Sale per indivisible quantity   | 1                                |
| Head type                       | Standard                         |
| Shape of signaling unit head    | Round                            |
| Type of operator                | spring return                    |
| Operator profile                | Red flush, unmarked              |
| Operator additional information | Clear boot                       |

## Complementary

|                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CAD overall width                  | 30 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| CAD overall height                 | 30 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| CAD overall depth                  | 37 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Product weight                     | 0.019 kg                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Resistance to high pressure washer | 7000000 Pa at 55 °C, distance : 0.1 m                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Mechanical durability              | 10000000 cycles                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Station name                       | XALD 1...5 cut-outs<br>XALK 2...5 cut-outs                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Cap/operator or lens colour        | Red                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Marking                            | Unmarked                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Electrical composition code        | M1 for <6 contacts using single blocks in front mounting with integral LED<br>M2 for <6 contacts using single and double blocks in front mounting with integral LED<br>M6 for <2 contacts using single blocks in front mounting with integral LED and transformer<br>M10 for <2 contacts using single blocks in front mounting with integral LED<br>MF1 for <2 contacts using single blocks in front mounting with integral LED<br>MR1 for <2 contacts using single blocks in rear mounting with integral LED |
| Device presentation                | Basic sub-assemblies                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Environment

|                                       |                                                                                                                                                                                |
|---------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TC                                                                                                                                                                             |
| Ambient air temperature for storage   | -40...70 °C                                                                                                                                                                    |
| Ambient air temperature for operation | -40...70 °C                                                                                                                                                                    |
| Overvoltage category                  | Class II conforming to IEC 60536                                                                                                                                               |
| IP degree of protection               | IP66 conforming to IEC 60529<br>IP67                                                                                                                                           |
| Enclosure Type                        | UL type 4X/13                                                                                                                                                                  |
| IK degree of protection               | IK05 conforming to IEC 62262                                                                                                                                                   |
| Standards                             | IEC 60947-5-1<br>CSA C22.2 No 14<br>IEC 60947-1<br>JIS C8201-5-1<br>GB 14048.5<br>UL 508<br>IEC 60947-5-4<br>JIS C8201-1                                                       |
| Product certifications                | CSA<br>DNV<br>BV<br>LROS (Lloyds register of shipping)<br>UL listed                                                                                                            |
| Vibration resistance                  | 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6                                                                                                                               |
| Shock resistance                      | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |

# Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 4.2 cm   |
| Package 1 Width              | 3.3 cm   |
| Package 1 Length             | 5.2 cm   |
| Package 1 Weight             | 20.0 g   |
| Unit Type of Package 2       | S01      |
| Number of Units in Package 2 | 75       |
| Package 2 Height             | 15.0 cm  |
| Package 2 Width              | 15.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 1.725 kg |

# Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better



### Materials and Substances

Average percentage of recycled plastic content16 %

Average percentage of recycled metal content29 %

Packaging made with recycled cardboardYes

Packaging without single use plasticYes

EU RoHS Directive[Compliant](#)

REACH Regulation[Reference contains Substances of Very High Concern above the threshold](#)

## Use Longer



### Lifetime extension

RepairNo

## Use Again



### Repack and remanufacture


End of life manual availability[End of Life Information](#)

Take-backNo

Dimensions Drawings

Dimensions


---



Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended ( $\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88 \text{ in. } \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$ )

| Connections                                   | a in mm | a in in. | b in mm | b in in. |
|-----------------------------------------------|---------|----------|---------|----------|
| By screw clamp terminals or plug-in connector | 40      | 1.57     | 30      | 1.18     |
| By Faston connectors                          | 45      | 1.77     | 32      | 1.26     |
| On printed circuit board                      | 30      | 1.18     | 30      | 1.18     |


Detail of Lug Recess



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended ( $\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88 \text{ in. } \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$ )

## Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

### Panel Cut-outs (Viewed from Installer's Side)




**A:** 30 mm min. / 1.18 in. min.

**B:** 40 mm min. / 1.57 in. min.

### Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)


Dimensions in mm



**A:** 30 mm min.

**B:** 40 mm min.

Dimensions in in.



A: 1.18 in. min.  
B: 1.57 in. min.


General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in.: T1 + T2 = 0.3 mm max.

Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB5AZ009: ± 2° 30' (excluding cut-outs marked a and b).
- Tightening torque of screws ZBZ006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB5AZ079 fixing collar/pillar and its fixing screws:
  - every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - with each selector switch head (ZB5AD\*, ZB5AJ\*, ZB5AG\*).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.



- (1) Head ZB5AD•
- (2) Panel
- (2) Nut
- (4) Printed circuit board

## Mounting of Adapter (Socket) ZBZ01•

- 1 2 elongated holes for ZBZ006 screw access
- 2 1 hole  $\varnothing$  2.4 mm  $\pm$  0.05 / 0.09 in.  $\pm$  0.002 for centring adapter ZBZ01•
- 3 8  $\times$   $\varnothing$  1.2 mm / 0.05 in. holes
- 4 1 hole  $\varnothing$  2.9 mm  $\pm$  0.05 / 0.11 in.  $\pm$  0.002, for aligning the printed circuit board (with cut-out marked **a**)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked **b**)
- 6 4 holes  $\varnothing$  2.4 mm / 0.09 in. for clipping in adapter ZBZ01•


Dimensions An + 18.1 relate to the  $\varnothing$  2.4 mm  $\pm$  0.05 / 0.09 in.  $\pm$  0.002 holes for centring adapter ZBZ01•.



Technical Description


Electrical Composition Corresponding to Codes M1 and M7

---




Electrical Composition Corresponding to Codes M2 and M8

---




Electrical Composition Corresponding to Codes M6 and P2

---



Electrical Composition Corresponding to Codes M5, M10, MF1, MR1 and MF2



Legend

---

Single contact



Double contact



Light block



Possible location



Image of product / Alternate images

Alternative

---










Image of product in real life situation

