

TF-SE25

Torque wrench TORCOFIX TF-SE

20-400 Nm / 15-300 lbf·ft

Code	ETIM
3288196	EC002132
EAN	UNSPSC
4010886965535	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-02-22
Customs tariff number	
82041100	



Article description

- Use:
- Controlled screw tightening in the range of 5 - 25 Nm / 3,7 - 18 lbf·ft
- Adjustable, releasing and sturdy tubular torque wrench with rectangular cavity for industry and the trades
- Features:
- Classified as per DIN EN ISO 6789-2:2017 Type II Class A; adjusted to a maximum permissible +/- 3 % deviation and thus with a greater precision than the standard-stipulated +/- 4 %
- Incl. traceable test certificate (DIN EN ISO 6789-2:2017)
- For controlled right- and left-hand tightening (insert tool for change of direction)
- Square Drive 9x12 mm with ejector aid
- Robust, matt powder-coated tubular steel construction, with galvanized ratchet and high-quality plastic parts
- New ergonomic handle, shaped according to the natural grip position of the hand
- Clearly recognisable and tactile hand centring aid and calibration aid in the middle of the handle
- Double scale Nm / lbf·ft and vernier are protected from abrasion and contamination by an enlarged viewing window
- With vernier scale for Nm main scale for setting intermediate scale values; lbf·ft setting only via main scale
- Vertical alignment of the scale, torque adjustment therefore suitable for left and right handers
- Scale line positioned directly above the scale prevents reading errors (parallax errors)
- Unit labeling integrated in the scale frame and also protected by viewing windows, • • The precise release mechanism generates a distinct tactile and audible release signal when the set torque value is reached
- Incl. roll away protection, prevents rolling away when the tool is put down

Article information

Contents (Qty of pieces)	1	Drive connector rectangular	9 x 12 mm
Net weight [kg]	0,3 kg	Backup	Catch lock
Total length [mm]	261,5 mm	Trigger mechanism	Short path triggering
Total width [mm]	39 mm	Precision +/-	+/- 3 %
Total height [mm]	39,8 mm	Direction of tightening	Left and right
Material	Steel tube construction with high-quality plastic parts	Fixed setting	no
Depth gauge [metric]	17,5 mm	Test certificate	DIN EN ISO 6789-2:2017
Drive type/drive	Rectangular cavity	Graduation	1
Torque [min.] [N·m]	5 Nm	Calibration length	261,5 mm
Torque [max.] [N·m]	25 Nm	Graduation [lbf·ft]	1 lbf·ft
Torque [min.] [lbf·ft]	3,7 lbf·ft	Graduation [N·m]	1 Nm
Torque [max.] [lbf·ft]	18 lbf·ft	vernier Nm	0,1 Nm
Torque range (min./max.) [N·m]	5 Nm - 25 Nm	Storage/Content	Plastic box
Torque range (min./max.) [lbf·ft]	3,7 lbf·ft - 18 lbf·ft		