

AI-S 1-8 TQ-25000 - Ferrule



2100081

<https://www.phoenixcontact.com/gb/products/2100081>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: turquoise

Your advantages

- Plastic collar with optimized diameter for 1.0 mm² cables, with max. insulation outside diameter of 2.8 mm
- Suitable for all PT 1,5/S terminal blocks and COMBI connectors with a width of 3.5 mm
- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper
- The insulation reliability of close connections is increased and the splicing of wires is prevented

Commercial data

Item number	2100081
Packing unit	25,000 pc
Minimum order quantity	25,000 pc
Sales key	BH3411
Product key	BH3411
GTIN	4067923213883
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85369010
Country of origin	DE

AI-S 1-8 TQ-25000 - Ferrule

2100081

<https://www.phoenixcontact.com/gb/products/2100081>



Technical data

Product properties

Product type	Cable end sleeve
Product property	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

Connection data

Conductor connection

Conductor cross section flexible max.	1 mm ²
Conductor cross section AWG max.	18
Stripping length	11 mm

Dimensions

Dimensional drawing	
Sleeve length	14 mm
Length contact range	8 mm
Maximum stripping length	11 mm
Ferrule diameter	1.5 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.25 mm
Inner dimensions of the insulating collar	2.8 mm

Material specifications

Color	turquoise green (RAL 5018)
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen


Mechanical properties

Technical data

Sleeve length	14 mm
---------------	-------

Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

AI-S 1-8 TQ-25000 - Ferrule



2100081

<https://www.phoenixcontact.com/gb/products/2100081>

Classifications

ECLASS

ECLASS-13.0	27400201
-------------	----------

ETIM

ETIM 9.0	EC000005
----------	----------

AI-S 1-8 TQ-25000 - Ferrule

2100081

<https://www.phoenixcontact.com/gb/products/2100081>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk