




## Data Sheet

ENGLISH


### Product: PEC Depth and Angle Gauges

#### Depth Gauges

	<p>Head manufactured from fully hardened steel            Base measurement: 2 1/2" wide x 1/8" thick            Top surface: 1" wide x 1/8" thick            Depth rule graduated both sides</p> <p>Squareness accuracy of Rule to Base: 90° ±15 min</p>
-----------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

RS Code	Rule Length	Front Face Graduated	Rear Face Graduated
724-4064	150mm / 6"	0-150mm in 1mm steps	0-6" in 1/32 steps

#### Combination Angle Depth Gauges

	<p>Head manufactured from fully hardened steel            Base measurement: 2 1/2" wide x 1/8" thick            Top surface: 1" wide x 1/8" thick            Head marked with angles: 30°, 45° and 60°</p> <p>Depth rule graduated both sides            Supplied with additional 6" depth rod: 0.096" diameter</p> <p>Squareness accuracy of Rule to Base: 90° ±15 min            Angle accuracy: ±30 min</p>
-------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

RS Code	Rule Length	Front Face Graduated	Rear Face Graduated
724-4061	150mm	0-150mm in 1mm steps	0-150mm in 1mm steps

#### Rule Scale Accuracy:

Rule Length	Any 2 adjacent Graduations; Plus	Any 2 adjacent Graduations; Minus	0 end to any Graduation: Plus	0 end to any Graduation: Minus
150mm / 6"	0.05mm / 0.002"	0.05mm / 0.002"	0.10mm / 0.004"	0.09mm / 0.0035"

In interpreting this accuracy chart, please note that the zero end of the rule end is defined as that rule end nearest the lowest graduation. The leading edge of a graduation is defined as the graduation closest to the rule end being used in the measurement. Therefore, the following accuracy statement is relative to the first graduation of each side, at a temperature of 72° ± 3°F