

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200490417](#)
Status: **Active**
Overview: Brad® Ethernet Solutions
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 26 AWG, PVC Cable, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
 Series [120049](#)
 Connector End A Micro-Change (M12)
 Connector End B Micro-Change (M12)
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad® Ethernet Solutions](#)
 Performance Category 5e
 Product Name Micro-Change (M12)
 Region America, Asia, Europe
 Type Double Ended
 UPC 883906170127

Physical

Cable Diameter 6.35mm (.250")
 Cable Length 1.0m (3.28')
 Color - Cable Jacket Blue Green
 Coupling Style Threaded
 Gender Male-Male
 Keyway D-coded
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold over Nickel
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -25°C to +75°C
 Wire Size AWG 26
 Wire/Cable Type Unshielded-Bonded

Electrical


Current - Maximum per Contact 1.5A
 Voltage - Maximum 125V

Material Info

Engineering Number E11A06002M010

Reference - Drawing Numbers

Sales Drawing SD-120049-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per -ED/01/2018 (15 January 2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120049 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION