

### Main

Range	New Unica
Product or component type	Thermostat
Device application	Room
Device presentation	Mechanism
Colour tint	Anthracite (RAL 7021)

### Complementary

Technology type	Electronic
[Ue] rated operational voltage	230 V AC +/- 10 % at 50 Hz
Load interrupting current	Resistive: 8 A Inductive: 5 A cos phi 0.8
Protection type	Thermal overload protection
Number of modules	2 modules
Clamping connection capacity	<= 2 x 2.5 mm <sup>2</sup> for flexible cable(s) <= 2 x 2.5 mm <sup>2</sup> for rigid cable(s)
Contacts type and composition	1 C/O
Connections - terminals	Screw terminals
Status LED	1 dual color LED (red/blue) heating or air-conditioning application 1 LED (green) presence of voltage
Marking	L+N OUT
Programmable temperature	No
Temperature setting range	5...30 °C
Measurement accuracy	0.5 °C
Material	PC (polycarbonate) GF10 FR: casing Metal: terminals Thermoplastic ABS-UV stabilised: central plate
Surface treatment	Painted
Surface finish	Matt
Device mounting	Flush
Fixing mode	Clip-in
Minimum mounting height	1.5 m
Depth	47 mm
Width	45 mm
Height	45 mm
Embedding depth	33 mm
Net weight	0.083 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Targeted channel	Professional
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	5...30 °C
Ambient air temperature for storage	-20...60 °C
Standards	EMC directive EN 60730-2-9 LV directive

## Offer Sustainability

EU RoHS Directive	Under investigation
Sustainable packaging	Yes