

LEDBHO15W

15W – 1000lm LED Energy Saver Bulkhead Light – Oval

Features & Benefits

- A powerful and energy saving alternative to standard bulkhead lights
- Wide light diffusion pattern
- Robust die cast housing with tough polycarbonate lens suitable for industrial, commercial and home installations
- IP65 weatherproof rating



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface Mount
Earth Class Rating	Class I
Operating Temperature	-10°C to +40°C
Ingress Protection Rating	IP65
Wattage	15
Beam Angle	120°
Energy Efficiency	Class G
Energy Usage	15.4KwH/1000H
Lumen output (lm)	1000

Data sheet

LEDBHO15W

Light / LED Lighting

Colour Temperature (K)	5000
LED Type	SMD (On LED Plate)
Mounting Hole Centres (mm)	176
Multiple Unit Support	Yes
Cable Entry(s)	Back Entry, Side Entry (Lip In Housing)

General

Weight (g)	469
Height (mm)	215
Width (mm)	131
Depth (mm)	69
Body Construction	Polycarbonate (Front Cover), Aluminium (Body)
Product Colour	Silver
Accessories (Included)	Fittings
EAN Number	5012483012673
Guarantee Period	3 Years

Line Diagrams

