

# SACC-FP-F-M12/M16 SMD PPI - Housing screw connection



1454494

<https://www.phoenixcontact.com/gb/products/1454494>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Socket, M12-Push-pull internal locking, Front mounting, M16, SMD

## Your advantages

- Plug and Produce: quick and reliable connection even in confined spaces
- Easy design-in: countersunk M12 ports for compact device concepts
- Highly future-proof: standardized product range for worldwide availability
- Greater flexibility: one M12 device connection for screw and push-pull connectors

## Commercial data

Item number	1454494
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABQCCB
Product key	ABQBAJ
GTIN	4063151843397
Weight per piece (including packing)	13.07 g
Weight per piece (excluding packing)	11.475 g
Customs tariff number	74198090
Country of origin	DE

# SACC-FP-F-M12/M16 SMD PPI - Housing screw connection



1454494

<https://www.phoenixcontact.com/gb/products/1454494>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	If necessary, order locking nut separately

### Product properties

Product type	Panel mounting base
Thread type	M12

### Connection data

Connection method	SMD
Tightening torque	2 ... 3 Nm

### Material specifications

Material	Brass, nickel-plated (Locking nut)
Seal material	FKM
	FKM
Material for screw connection	Brass, nickel-plated

### Connector

#### Connection 1

Head design	Socket
Head thread type	M12
Head locking type	Push-pull internal locking

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection (when plugged in)	IP65/IP67 (correctly plugged in and locked)
Degree of protection	IP65/IP67 (correctly plugged in and locked)
	IP67, when in locked state
	IP65, when in locked state
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

# SACC-FP-F-M12/M16 SMD PPI - Housing screw connection



1454494

<https://www.phoenixcontact.com/gb/products/1454494>

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	based on IEC 61076-2-010

## Mounting

Mounting type	Front mounting M16
---------------	--------------------

# SACC-FP-F-M12/M16 SMD PPI - Housing screw connection



1454494

<https://www.phoenixcontact.com/gb/products/1454494>

## Classifications

### ECLASS

ECLASS-13.0	27440224
-------------	----------

### ETIM

ETIM 9.0	EC003556
----------	----------

# SACC-FP-F-M12/M16 SMD PPI - Housing screw connection



1454494

<https://www.phoenixcontact.com/gb/products/1454494>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)