



Product data sheet

Power tools for trade & industry

Laser Measure

GLM 80



The high-tech solution for convenient measurement

The most important data

Measurement range	0.05 – 80.00 m
Laser diode	635 nm, < 1 mW
Weight, approx.	0.14 kg

Part Number 0 601 072 370

[> More product information](#)

Technical data

Technical data

Laser diode	635 nm, < 1 mW
Measurement range	0.05 – 80.00 m
Laser class	2
Measurement accuracy, typical	± 1.5 mm* (*plus use-dependent deviation)
Measurement time, typical	< 0.5 s
Measurement time, max.	4 s
Power supply	1 x 3.7 V Li-Ion battery (1250 mAh)
Automatic deactivation	5 min
Weight, approx.	0.14 kg
Units of measurement	m/cm/mm
Memory capacity (values)	20 + 1
Dust and splash protection	IP 54
Laser colour	Red

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High functionality due to integrated 360° incline sensor
- Precise and easy to operate due to illuminated display which flips automatically depending on the orientation of the instrument
- Up to 25,000 individual measurements per battery charge due to Li-Ion technology

