

ÖLFLEX® CLASSIC FD 810 P

Highly flexible control cable with PVC core insulation and abrasion and oil resistant PUR sheath

ÖLFLEX® CLASSIC FD 810 P - Power and control cable for versatile use in power chains in harsh environmental conditions

Info

Core Line for ordinary duty in power chain applications

Good oil resistance



UV-resistant



Power chain



Oil-resistant



Mechanical resistance

Benefits

Well-proven and reliable

Various applications

Increased durability under harsh conditions thanks to robust PUR outer sheath

Resistant to contact with many mineral oil-based lubricants, diluted acids, aqueous alkaline solutions and other chemical media

Application range

In power chains or moving machine parts

Particularly in wet areas of machine tools and transfer lines

Power circuits for electrical equipments used in automation engineering

Suitable for use in measuring, control and regulating circuits

In dry, damp or wet interiors with normal mechanical stress conditions

ÖLFLEX® CLASSIC FD 810 P

Product features

Designed for 5 million alternating bending cycles and travel distances up to 10 meter
Flame-retardant according to IEC 60332.1.2
High oil-resistance
Abrasion and notch-resistant
Low-adhesive surface

Norm references / Approvals

Core based on VDE 0245/0285
Outer sheath based on VDE 0245/0285
For use in power chains: Please comply with assembly guideline Appendix T3

Product Make-up

Extra-fine wire strand made of bare copper wires (class 6)
Core insulation: PVC
Cores twisted in short lay lengths
Non-woven wrapping
PUR outer sheath, grey (RAL 7001)

Technical Data

Classification:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Core identification code:	Black with white numbers acc. to VDE 0293-1
Conductor stranding:	Extra-fine wire according to VDE 0295, class 6/IEC 60228 class 6
Minimum bending radius:	For flexible use: 7.5 x outer diameter Fixed installation: 4 x outer diameter
Nominal voltage:	U0/U: 300/500 V
Test voltage:	4000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Flexing: -5°C to +70°C Fixed installation: -40°C to +80°C

Note

Unless specified otherwise, the shown product values are nominal values at room temperature. You can receive further values, such as tolerances, upon request if they are available and have been released for publication.

Copper price basis: EUR 150/100 kg; see catalogue appendix T17 for the application and definition of "Metal price basis" and "Metal index"

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging: Ring ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred packaging (e.g. 1 x 500 m drum or 5 x 100 m rings)

Photographs are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® CLASSIC FD 810 P**

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® CLASSIC FD 810 P				
0026300	2 X 0.5	5.3	10	36
0026301	3 G 0.5	5.7	15	44
0026302	4 G 0.5	6.3	19	53
0026303	5 G 0.5	6.8	24	62
0026304	7 G 0.5	8	34	82
0026305	12 G 0.5	9.5	58	129
0026306	18 G 0.5	11.4	86.4	185
0026319	2 X 0.75	5.7	15	44
0026320	3 G 0.75	6.2	22	55
0026321	4 G 0.75	6.8	29	67
0026322	5 G 0.75	7.4	37	80
0026323	7 G 0.75	8.9	51	109
0026324	12 G 0.75	10.6	87	172
0026326	18 G 0.75	12.7	130	247
0026327	25 G 0.75	15.2	181	346
0026330	2 X 1	6.1	20	52
0026331	3 G 1	6.6	29	66
0026332	4 G 1	7.3	39	82
0026333	5 G 1	8	48	97
0026334	7 G 1	9.6	67	117
0026335	12 G 1	11.4	115	211
0026338	18 G 1	13.9	173	310
0026339	25 G 1	16.4	240	426
0026341	34 G 1	18.9	326.4	571
0026342	41 G 1	20.6	394	684
0026343	50 G 1	22.3	480	822
0026344	65 G 1	25.4	624	1058
0026349	2 X 1.5	6.8	29	68
0026350	3 G 1.5	7.4	43.2	86
0026351	4 G 1.5	8.1	58	106
0026352	5 G 1.5	9.1	72	131
0026353	7 G 1.5	10.9	101	178
0026354	12 G 1.5	12.9	173	281

Last Update (19.07.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16

**ÖLFLEX® CLASSIC FD 810 P**

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
0026355	16 G 1.5	14.6	230	365
0026356	18 G 1.5	15.6	259	411
0026357	25 G 1.5	18.6	360	571
0026359	34 G 1.5	21.1	489.6	753
0026361	42 G 1.5	23	629	919
0026362	50 G 1.5	25	720	1093
0026370	3 G 2.5	9	72	135
0026371	4 G 2.5	10	96	168
0026372	5 G 2.5	11.2	120	206
0026373	7 G 2.5	13.6	168	286
0026374	12 G 2.5	16	288	453
0026375	14 G 2.5	17.2	336	525
0026381	4 G 4	11.7	160	252
0026382	5 G 4	13.1	200	309
0029200	1 G 6	6.4	60	84
0026383	4 G 6	13.9	230	377
0029210	1 G 10	7.7	100	141
0026385	4 G 10	17.6	384	614
0026386	5 G 10	19.6	480	751
0029220	1 G 16	9.2	160	198
0026387	4 G 16	21	615	851

Last Update (19.07.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet:
PN 0456 / 02_03_16