




## Flame-retardant, high-expansion polyester braided sleeving

### Helagaine HEGPVOX

Helagaine HEGPVOX braided sleeving is especially suitable wherever fire protection is important, such as in railway vehicles.

#### Features and benefits

- Made of sturdy polyester
- Self-extinguishing according to UL94 V0 for enhanced fire protection
- Highly flexible
- Expands to 3x nominal diameter
- Easy to apply over irregular shapes
- Good abrasion resistance



Helagaine HEGPVOX flame-retardant braided sleeving.

<b>MATERIAL</b>	Polyester (PBT)
<b>Operating Temperature</b>	-50 °C to +150 °C, intermittent +200 °C
<b>Melting Point</b>	+225 °C
<b>Flammability</b>	UL94 V0, FMVSS 302



TYPE	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Tools	Article-No.
<b>HEGPVOX03</b>	2	6	Black with White Identification Yarn (BKIDWH)	200 m	45	170-50030
<b>HEGPVOX06</b>	3	10	Black with White Identification Yarn (BKIDWH)	200 m	45	170-50060
<b>HEGPVOX09</b>	5	16	Black with White Identification Yarn (BKIDWH)	100 m	45	170-50090
<b>HEGPVOX12</b>	6	19	Black with White Identification Yarn (BKIDWH)	100 m	45	170-50120
<b>HEGPVOX20</b>	12	32	Black with White Identification Yarn (BKIDWH)	100 m	45	170-50200
<b>HEGPVOX30</b>	19	45	Black with White Identification Yarn (BKIDWH)	50 m	45	170-50300
<b>HEGPVOX40</b>	32	70	Black with White Identification Yarn (BKIDWH)	50 m	45	170-50400
<b>HEGPVOX50</b>	38	76	Black with White Identification Yarn (BKIDWH)	50 m	45	170-50500

All dimensions in mm. Subject to technical changes.

Colour grey available on request. Cuts in any lengths. Minimum Order Quantity (MOQ) may differ from package content.

Recommended Tools	
	45 HSG0
	572

For more information on toolings please refer to the Application Tooling chapter.



For product specific approvals and specifications please refer to the Appendix.