



This device is an industrial PoE injector with two Gigabit ETHERNET ports. An ETHERNET port (IEEE 802.3 af/at/bt/4PPoE) provides power to PoE (Powered over Ethernet) devices with up to 71 W. The power output of the PoE injector (Power Sourcing Equipment) is up to 90 W. Additionally, automatic transmission rate detection (auto-negotiation) and automatic detection of the transmit and receive lines (Auto MDI-X) allow simple plug-and-play operation.

Its compact design with a DIN-rail adapter simplifies installation in control cabinets, offering high resistance to temperature, vibration, and shock. The integrated voltage transformer allows operation with the standard 24 VDC supply voltage used in control cabinets. Meaningful status LEDs, a redundant power supply, and an alarm contact configurable via a DIP switch enhance the availability of the PoE injector during operation and ensure easy handling.

Typical applications:

- Connecting vending machines or camera systems
- Connecting intelligent PoE-capable lighting systems
- Connecting decentralized control cabinets when using a PoE splitter

Features:

- Redundant DC power supply
- Supply voltage range: 24 ... 57 VDC
- DIP switch to set alarm functions
- Full compliance with IEEE 802.3, 802.3u and 802.3ab standards
- Autonegotiation at both 10/100/1000BASE-T ports
- Auto-MDI/MDIX (crossover) at both 10/100/100BASE-TX ports

Technical data		
Number of 1 Gb/s ports	2	
Communication standards	IEEE 802.3 10BASE-T IEEE 802.3u 100BASE-TX IEEE 802.3ab 1000BASE-T IEEE 802.3af Power over Ethernet (PoE) IEEE 802.3at High Power over Ethernet (PoE+) IEEE 802.3bt 4-pair PoE	
Supply voltage	24 ... 57 VDC	
Power consumption (max.)	120 W	
Current consumption (max.)	5000 mA	
Transmission rate	Copper cable: 100/1000 Mbit/s	
Transmission medium (communication/fieldbus)	Copper cable: Cat. 5e or 6a , 100 m maximum cable length	
Indicators	Device: LED (PWR, RPS, PoE, NBT) green: Supply voltage (primary), redundant supply voltage (secondary), Power over Ethernet, mode; LED (ALM, OL 93-96 W) red: Alarm, Overload; LED (PoE Usage (Watt)) green: 15, 30, 60, 90 Watt; per port: LED green: Status 1000 Mbit/s, LNK/ACT port	



Connection data	
Connection technology: communication/fieldbus	Copper cable: 2 x RJ-45
Connection technology: supply	1 x Built-in male connector: 231-436/001-000; included female connector (MCS Connectors): 2231-106/026-000

Physical data	
Width	25 mm / 0.98 inches
Height	116 mm / 4.57 inches
Depth	100 mm / 3.93 inches

Mechanical data	
Weight	243.8 g
Housing material	Aluminum
Conformity marking	CE

Environmental requirements	
Ambient temperature (operation)	-40 ... +75 °C
Ambient temperature (storage)	-40 ... +80 °C
Protection type	IP30
Relative humidity (without condensation)	95 %
Mounting type	DIN-35 rail
Vibration resistance	per IEC 60068-2-6
Shock resistance	per IEC 60068-2-27
EMC immunity to interference	Per EN IEC 61000-6-2
EMC emission of interference	Per EN IEC 61000-6-4
Fire load	0 MJ

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	TW
GTIN	4066966511772
Customs tariff number	85176200000

Product classification	
UNSPSC	39121006
ETIM 9.0	EC003552
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption



Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
KC National Radio Research Agency	Article 58-2, Clause 3	MSIP-REM-W43-ISW852
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 61010-2-201	E175199

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
SDoC for FCC WAGO GmbH & Co. KG	-	-
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 852-1732



Documentation

Manual			
Product Manual Industrial PoE Injector	3421572875 3 en-US 8/21/2024 13:26 22.08.2024	pdf 12661.51 KB	

