

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (.6% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 1056456-1
[2837 7316 02](#)



TE Part # 1056462-1
[2837 7388 02](#)




TE Part # 1050525-1
[2001 5003 02,SMA CABLE PLUG](#)




TE Part # 1050548-1
[2001 5032 02](#)


Also in the Series | SMA




[Battery Holders\(1\)](#)




[Connector Adapters & Connector Savers\(8\)](#)



[Connector Caps & Covers\(3\)](#)



[Connector Strain Relief\(1\)](#)



[RF Cable Assemblies\(2\)](#)

Customers Also Bought



TE Part #60214-2
[187 FASTON REC 20-16 AWG TPBR](#)



TE Part #5-1625971-6
[HSA25 50R 5%](#)



TE Part #NB07752001
[HTAT-24/6-0-STK](#)



TE Part #228553-1
[SMB COMML BLKHD ADAPTER](#)





TE Part #6609107-2
[PS0SXDS60=C1027](#)



TE Part #205842-1
[CPC PLUG ASSEMBLY SIZE 23-63](#)



TE Part #1051664-1
[2031 5012 00](#)



TE Part #1051660-1
[2031 5011 00](#)

TE Part #1589333-1
[335-0002-01 = HARDWARE](#)

TE Part #GA100K10A5I
[DISC- - BTC](#)

Documents

Product Drawings

[2080 1900 00](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1053492-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1053492-1_A.3d_igs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

[Product Specification](#)

English