

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : ULTRAFORM 1060
UFI : 7JE0-U0R6-D00J-WA2D

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Industrial use, Professional use
Industrial/Professional use spec : For professional use only
Industrial
Use of the substance/mixture : Lubricants, Greases and Release Products

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer

ROCOL a division of ITW Ltd
Rocol House
Wakefield Rd, Swillington
LS26 8BS Leeds - United Kingdom
T +44 (0)113 232 2600
customer.service@rocol.com - www.rocol.com

1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Flammable liquids, Category 3 H226
Specific target organ toxicity — Single exposure, Category 3, Narcosis H336
Aspiration hazard, Category 1 H304
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



ULTRAFORM 1060

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Signal word (CLP)	: Danger
Contains	: HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS
Hazard statements (CLP)	: H226 - Flammable liquid and vapour. H304 - May be fatal if swallowed and enters airways. H336 - May cause drowsiness or dizziness.
Precautionary statements (CLP)	: P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P261 - Avoid breathing dust/fume/gas/mist/vapours/spray. P301+P310+P331 - IF SWALLOWED: Immediately call a POISON CENTER or doctor. Do NOT induce vomiting. P303+P361+P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water . P304+P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing. P312 - Call a POISON CENTRE or doctor if you feel unwell.
EUH-statements	: EUH066 - Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS substance with a Community workplace exposure limit	(CAS-No.) 64742-48-9 (EC-No.) 919-857-5 (REACH-no) 01-2119463258-33	≥ 70	Flam. Liq. 3, H226 STOT SE 3, H336 Asp. Tox. 1, H304
PHOSPHATE ALKYL AMINE DERIVATIVE	(CAS-No.) 80939-62-4 (EC-No.) 279-632-6 (REACH-no) 01-2119976322-36	1 – 2.4	Skin Irrit. 2, H315 Eye Irrit. 2, H319 Aquatic Chronic 2, H411

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER/doctor if you feel unwell.
First-aid measures after eye contact	: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Immediately call a POISON CENTER/doctor.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after inhalation	: May cause drowsiness or dizziness.
-----------------------------------	--------------------------------------

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

ULTRAFORM 1060

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 5: Firefighting measures

5.1. Extinguishing media

- Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

- Fire hazard : Flammable liquid and vapour.
Explosion hazard : May form flammable/explosive vapour-air mixture.

5.3. Advice for firefighters

- Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

- General measures : Remove ignition sources. Use special care to avoid static electric charges. No open flames. No smoking.

6.1.1. For non-emergency personnel

- Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

- Protective equipment : Equip cleanup crew with proper protection. Avoid breathing dust/fume/gas/mist/vapours/spray.
Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

- Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Additional hazards when processed : Handle empty containers with care because residual vapours are flammable.
Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. No open flames. No smoking. Take precautionary measures against static discharge. Use only non-sparking tools. Avoid breathing dust/fume/gas/mist/vapours/spray. Use only outdoors or in a well-ventilated area.

7.2. Conditions for safe storage, including any incompatibilities

- Technical measures : Proper grounding procedures to avoid static electricity should be followed. Ground/bond container and receiving equipment. Use explosion-proof electrical/ventilating/lighting equipment.
Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Keep container tightly closed.

ULTRAFORM 1060

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight. Heat sources.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS (64742-48-9)	
EU - Indicative Occupational Exposure Limit (IOEL)	
Local name	White spirit Type 3
IOEL TWA	116 mg/m ³
IOEL TWA [ppm]	20 ppm
IOEL STEL	290 mg/m ³
IOEL STEL [ppm]	50 ppm
Notes	Skin. (Year of adoption 2007)
Regulatory reference	SCOEL Recommendations

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

No additional information available

8.2.2. Personal protection equipment

Personal protective equipment:

Avoid all unnecessary exposure.

8.2.2.1. Eye and face protection

Eye protection:

Chemical goggles or safety glasses

8.2.2.2. Skin protection

Hand protection:

Wear protective gloves. Nitrile rubber gloves

8.2.2.3. Respiratory protection

ULTRAFORM 1060

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Respiratory protection:

Where exposure through inhalation may occur from use, respiratory protection equipment is recommended. [In case of inadequate ventilation] wear respiratory protection. Wear a respirator conforming to EN140 with Type A filter or better

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Colourless.
Odour	: Characteristic odour.
Odour threshold	: No data available
pH	: No data available.
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available.
Freezing point	: No data available
Boiling point	: No data available
Flash point	: > 36 °C
Auto-ignition temperature	: > 200 °C
Decomposition temperature	: No data available
Flammability (solid, gas)	: No data available
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 0.87
Solubility	: No data available
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: 2 mm ² /s
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Flammable liquid and vapour.

10.2. Chemical stability

Flammable liquid and vapour. May form flammable/explosive vapour-air mixture.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures. Open flame. Overheating. Heat. Sparks.

ULTRAFORM 1060

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide. May release flammable gases.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS (64742-48-9)

LD50 oral rat	> 5000 mg/kg
LD50 dermal rat	> 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 402 (Acute Dermal Toxicity)
LD50 dermal rabbit	≥ 3160 mg/kg bodyweight Animal: rabbit, Guideline: OECD Guideline 402 (Acute Dermal Toxicity)
LD50 dermal	> 5000 mg/kg

PHOSPHATE ALKYL AMINE DERIVATIVE (80939-62-4)

LD50 oral rat	> 5000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 401 (Acute Oral Toxicity)
LD50 dermal rat	> 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 402 (Acute Dermal Toxicity)

Skin corrosion/irritation : Not classified
pH: No data available.

Additional information : Repeated exposure may cause skin dryness or cracking.

Serious eye damage/irritation : Not classified
pH: No data available.

Additional information : Based on available data, the classification criteria are not met

Respiratory or skin sensitisation : Not classified

Additional information : Based on available data, the classification criteria are not met

Germ cell mutagenicity : Not classified

Additional information : Based on available data, the classification criteria are not met

Carcinogenicity : Not classified

Additional information : Based on available data, the classification criteria are not met

Reproductive toxicity : Not classified

Additional information : Based on available data, the classification criteria are not met

STOT-single exposure : May cause drowsiness or dizziness.

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS (64742-48-9)

LOAEC (inhalation, rat, gas)	0
STOT-single exposure	May cause drowsiness or dizziness.

STOT-repeated exposure : Not classified

Additional information : Based on available data, the classification criteria are not met

ULTRAFORM 1060

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

PHOSPHATE ALKYL AMINE DERIVATIVE (80939-62-4)

LOAEL (oral, rat, 90 days)	10 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test), Guideline: other:EPA OPPTS 870.3650 (Combined Repeated Dose Toxicity Study with the Reproduction/Developmental Toxicity Screening Test)
----------------------------	---

Aspiration hazard : May be fatal if swallowed and enters airways.

ULTRAFORM 1060

Viscosity, kinematic	2 mm ² /s
----------------------	----------------------

Potential adverse human health effects and symptoms : Based on available data, the classification criteria are not met

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, short-term (acute) : Not classified
Hazardous to the aquatic environment, long-term (chronic) : Not classified

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS (64742-48-9)

LC50 - Fish [1]	> 1000 mg/l
-----------------	-------------

PHOSPHATE ALKYL AMINE DERIVATIVE (80939-62-4)

EC50 - Crustacea [1]	> 1 mg/l Test organisms (species): Daphnia magna
EC50 72h - Algae [1]	> 10 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
EC50 72h - Algae [2]	7.1 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)

12.2. Persistence and degradability

ULTRAFORM 1060

Persistence and degradability	Not established.
-------------------------------	------------------

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS (64742-48-9)

Persistence and degradability	Not established.
-------------------------------	------------------

12.3. Bioaccumulative potential

ULTRAFORM 1060

Bioaccumulative potential	Not established.
---------------------------	------------------

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS (64742-48-9)

Bioaccumulative potential	Not established.
---------------------------	------------------

12.4. Mobility in soil

No additional information available

ULTRAFORM 1060

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods





Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

Additional information : Handle empty containers with care because residual vapours are flammable.

Ecology - waste materials : Avoid release to the environment. Hazardous waste due to toxicity.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
UN 3295	UN 3295	Not applicable	UN 3295	UN 3295
14.2. UN proper shipping name				
HYDROCARBONS, LIQUID, N.O.S.	HYDROCARBONS, LIQUID, N.O.S.	Not applicable	HYDROCARBONS, LIQUID, N.O.S.	HYDROCARBONS, LIQUID, N.O.S.
Transport document description				
UN 3295 HYDROCARBONS, LIQUID, N.O.S. ((Hydrocarbons, C9-C11, n- alkanes, isoalkanes, cyclics, < 2% aromatics)), 3, III, (D/E)	UN 3295 HYDROCARBONS, LIQUID, N.O.S. ((Hydrocarbons, C9-C11, n- alkanes, isoalkanes, cyclics, < 2% aromatics)), 3, III	Not applicable	UN 3295 HYDROCARBONS, LIQUID, N.O.S. ((Hydrocarbons, C9-C11, n- alkanes, isoalkanes, cyclics, < 2% aromatics)), 3, III	UN 3295 HYDROCARBONS, LIQUID, N.O.S. ((Hydrocarbons, C9-C11, n- alkanes, isoalkanes, cyclics, < 2% aromatics)), 3, III
14.3. Transport hazard class(es)				
3	3	Not applicable	3	3
		Not applicable		
14.4. Packing group				
III	III	Not applicable	III	III
14.5. Environmental hazards				
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No	Dangerous for the environment : No	Dangerous for the environment : No
No supplementary information available				

14.6. Special precautions for user

Overland transport


Classification code (ADR) : F1

ULTRAFORM 1060

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Limited quantities (ADR)	: 5I
Excepted quantities (ADR)	: E1
Packing instructions (ADR)	: P001, IBC03, LP01, R001
Mixed packing provisions (ADR)	: MP19
Portable tank and bulk container instructions (ADR)	: T4
Portable tank and bulk container special provisions (ADR)	: TP1, TP29
Tank code (ADR)	: LGBF
Vehicle for tank carriage	: FL
Transport category (ADR)	: 3
Special provisions for carriage - Packages (ADR)	: V12
Special provisions for carriage - Operation (ADR)	: S2
Hazard identification number (Kemler No.)	: 30
Orange plates	:



Tunnel restriction code (ADR)	: D/E
EAC code	: 3YE

Transport by sea

Special provisions (IMDG)	: 223
Limited quantities (IMDG)	: 5 L
Excepted quantities (IMDG)	: E1
Packing instructions (IMDG)	: P001, LP01
IBC packing instructions (IMDG)	: IBC03
Tank instructions (IMDG)	: T4
Tank special provisions (IMDG)	: TP1, TP29
EmS-No. (Fire)	: F-E
EmS-No. (Spillage)	: S-D
Stowage category (IMDG)	: A
Properties and observations (IMDG)	: Immiscible with water.

Air transport

No data available

Inland waterway transport

Classification code (ADN)	: F1
Limited quantities (ADN)	: 5 L
Excepted quantities (ADN)	: E1
Equipment required (ADN)	: PP, EX, A
Ventilation (ADN)	: VE01
Number of blue cones/lights (ADN)	: 0

Rail transport

Classification code (RID)	: F1
Limited quantities (RID)	: 5L
Excepted quantities (RID)	: E1
Packing instructions (RID)	: P001, IBC03, LP01, R001
Mixed packing provisions (RID)	: MP19
Portable tank and bulk container instructions (RID)	: T4
Portable tank and bulk container special provisions (RID)	: TP1, TP29
Tank codes for RID tanks (RID)	: LGBF
Transport category (RID)	: 3
Special provisions for carriage – Packages (RID)	: W12
Colis express (express parcels) (RID)	: CE4
Hazard identification number (RID)	: 30

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

ULTRAFORM 1060

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:	
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Asp. Tox. 1	Aspiration hazard, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Skin Irrit. 2	Skin corrosion/irritation, Category 2
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H226	Flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.
EUH066	Repeated exposure may cause skin dryness or cracking.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.