

US-PML-W100 (50X50) CUS - Warning label



1014129

<https://www.phoenixcontact.com/in/products/1014129>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning label, can be ordered: by card, yellow/black, labeled according to customer specifications: Blank, mounting type: adhesive, diameter: 0 mm, Number of individual labels: 6, text field height: 50 mm, text field width: 50 mm



Your advantages

- UniSheet - stick-on warning labels, marked according to customer specifications
- Suitable for indoor and outdoor use
- The warning labels conform to the ISO 7010 international standard
- Highly flexible, soft PVC label that adapts well to uneven surfaces

Commercial data

Item number	1014129
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG8
Product key	BG8159
Catalog page	Page 320 (C-5-2013)
GTIN	4046356786706
Weight per piece (including packing)	5.36 g
Weight per piece (excluding packing)	5.36 g
Customs tariff number	49119900
Country of origin	PL

US-PML-W100 (50X50) CUS - Warning label



1014129

<https://www.phoenixcontact.com/in/products/1014129>

Technical data

Product properties

Product type	Warning label printed
Area of application	Warning labels
	Warning identification according to ISO 7010
Type	Triangle

Marking

Number of individual labels	6
Printing	Blank
Identification technology	Thermal transfer for sheets and cards

Dimensions

Width	50 mm
Text field width	50.00 mm
Height	43.3 mm
Text field height	50.00 mm
Length	50 mm
Diameter	0.00 mm

Material specifications

Color	yellow/black
Material	PVC
Components	Silicone-free

Environmental and real-life conditions

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

US-PML-W100 (50X50) CUS - Warning label



1014129

<https://www.phoenixcontact.com/in/products/1014129>

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	ISO 22479:2019-05
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 10 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

US-PML-W100 (50X50) CUS - Warning label



1014129

<https://www.phoenixcontact.com/in/products/1014129>

Classifications

ECLASS

ECLASS-11.0	40200203
ECLASS-12.0	40200203
ECLASS-13.0	40200203

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

US-PML-W100 (50X50) CUS - Warning label



1014129

<https://www.phoenixcontact.com/in/products/1014129>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in