



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:51 (UTC)

MOTION & CONTROL
NSK



24124CE4

Spherical Roller Bearings

Boundary Dimensions


d	120	mm	Bore diameter
D	200	mm	Outside diameter
B	80	mm	Width
r (min.)	2	mm	Chamfer dimension

Basic Load Ratings

Cr	720000	N	Basic dynamic load rating
C0r	950000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	2000	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	3000	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	1400	min-1	Grease lubrication
Oil (Oil-bath)	1800	min-1	Oil-bath lubrication



Abutment and Fillet Dimensions

da (min.)	130	mm	Diameter of shaft abutment
da (max.)	136	mm	Diameter of shaft abutment
Da (min.)	171	mm	Diameter of housing abutment
Da (max.)	190	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

e	0.37	Constant
Y2	2.7	Axial load Factors
Y3	1.8	Axial load Factors
Y0	1.8	Axial load Factors

Mass

Mass approx.	10	kg	Mass approx.
--------------	----	----	--------------

