

PRODUCT-DETAILS

GSB128

2-PC INNER SLVE CONN SLV I.D. 0.128



General Information

Extended Product Type	GSB128
Product ID	7TAI029060R0003
EAN	5414363113652
Catalog Description	2-PC INNER SLVE CONN SLV I.D. 0.128
Long Description	Two Piece Inner Sleeve Connector for Hexagonal Range, Length 5/16 Inch/7.9mm, Inner Diameter .128 Inches/3.25mm, Outer Diameter .152 Inches/3.86mm, Color Silver, Hard Bronze, Tin Plated

Ordering

EAN	5414363113652
UPC	786210812977

Dimensions

Product Net Length	0, mm
--------------------	-------

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	2.8 in 71 mm
Package Level 1 Height	2.3 in

	58 mm
Package Level 1 Depth / Length	3.3 in 84 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	6.5 in 165 mm
Package Level 2 Height	4 in 102 mm
Package Level 2 Depth / Length	12.25 in 311 mm

Additional Information

Brand / Label	Sta-Kon
Color	Gray
Effective Date	19680516
Material	Hard Bronze
Number of Batteries	0
Product Name	STA-KON AND CATAMOUNT TERMINAL
Product Type	Two-Piece Inner Sleeve Connector
Special Functions	Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Hexagonal Range (the corresponding outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GSB128
Instructions and Manuals	GSB128
RoHS Information	9AKK107992A4006

Classifications

ETIM 6	EC002650 - Connection for screened wires
ETIM 7	EC002650 - Connection for screened wires
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

