

**FAG****6240-M**

Deep groove ball bearing

Deep groove ball bearing 62...-M, single row,
solid brass cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	M	Solid brass cage, rolling element guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S1	Rings dimensional stabilized up to 200°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	200 mm	Bore diameter
D	360 mm	Outside diameter
B	58 mm	Width
C _r	270,000 N	Basic dynamic load rating, radial
C _{0r}	310,000 N	Basic static load rating, radial
C _{ur}	12,800 N	Fatigue load limit, radial
n _G	3,200 1/min	Limiting speed
n _{gr}	2,430 1/min	Reference speed
≈m	27 kg	Weight



Mounting dimensions

$d_{a\min}$	217 mm	Minimum diameter shaft shoulder
$D_{a\max}$	343 mm	Maximum diameter of housing shoulder
$r_{a\max}$	3 mm	Maximum fillet radius

Dimensions

$r_{\min}$	4 mm	Minimum chamfer dimension
D_1	306.45 mm	Shoulder diameter outer ring
d_1	254.9 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

f_0	15.2	Calculation factor
-------	------	--------------------

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Axial load in two directions
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed
- 

Large bearing