



Image may differ from product. See technical specification for details.

C 3224

CARB toroidal roller bearing

CARB toroidal roller bearings are unique: as well as accommodating misalignment without increased stress levels, they also provide frictionless axial movement within the bearing in the non-locating position in self-aligning bearing arrangements. Being SKF Explorer

bearings, they can accommodate higher load levels and provide significantly extended service life.

- Accommodate misalignment and axial displacement within the bearing
- High radial load carrying capacity
- Provide frictionless axial movement
- Long bearing system life
- Reduce noise and vibration levels

Overview

Dimensions

Bore diameter	120 mm
Outside diameter	215 mm
Width	76 mm

Performance

Basic dynamic load rating	750 kN
Basic static load rating	980 kN
Reference speed	2 400 r/min
Limiting speed	3 200 r/min
SKF performance class	SKF Explorer


Properties

Number of rows	1
Locating feature, bearing outer ring	Without
Bore type	Cylindrical
Cage	Sheet metal
Radial internal clearance	CN
Tolerance class	Normal
Sealing	Without
Lubricant	None
Relubrication feature	Without
Candidate for remanufacturing	Yes

Logistics


Product net weight	11.5 kg
eClass code	23-05-09-13
UNSPSC code	31171505

Technical specification



Dimensions

d	120 mm	Bore diameter
D	215 mm	Outside diameter
B	76 mm	Width
d ₂	≈ 149 mm	Shoulder diameter of inner ring
D ₁	≈ 190 mm	Shoulder or recess diameter of outer ring
s ₁	max. 17.1 mm	Permissible axial displacement
r _{1,2}	min. 2.1 mm	Chamfer dimension



Abutment dimensions

d_a	min. 132 mm	Diameter of shaft abutment
d_a	max. 162 mm	Diameter of shaft abutment
D_a	min. 179 mm	Diameter of housing abutment
D_a	max. 203 mm	Abutment diameter housing
C_a	min. 2.4 mm	Minimum width of space required in housing
r_a	max. 2 mm	Radius of fillet
A negative value for C_a is theoretical.		Notes - Bullet list

Calculation data

SKF performance class		SKF Explorer
Basic dynamic load rating	C	750 kN
Basic static load rating	C_0	980 kN
Fatigue load limit	P_u	98 kN
Reference speed		2 400 r/min
Limiting speed		3 200 r/min
Misalignment factor	k_1	0.103
Internal clearance factor	k_2	0.108

Tolerances and clearances

GENERAL BEARING SPECIFICATIONS

- Tolerances: Normal, P5, tapered bore 1:12, tapered bore 1:30
- Radial internal clearance: cylindrical bore, tapered bore

BEARING INTERFACES

- [Seat tolerances for standard conditions](#)
- [Tolerances and resultant fit](#)

More Information

 Product details Designs and variants General bearing specifications Loads Temperature limits Permissible speed Design considerations Mounting Designation system	 Engineering information Principles of rolling bearing selection General bearing knowledge Bearing selection process Bearing failure and how to prevent it	 Tools SimPro Quick SKF Product select - Select and evaluate bearing SKF Product select - Combine bearing with housing LubeSelect for SKF greases Drive-up Method Program Heater selection tool Oil Injection Method Program Tool and Accessory Selector for sleeves and shafts
--	---	--



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.