



Part Number: 549945

PTZ, RG-59 #20, #18-2c, CMG, Siamese

Product Description

PTZ (CCTV + Power/Audio) Cable, Rated-CMG, 1-RG59 20 AWG solid bare copper with foam polyethylene, 95% bare copper braid, 1-18 AWG stranded bare copper pair with polypropylene insulation unshielded, Siamese with PVC jacket

Technical Specifications

Suitable Applications:	CCTV plus Audio, Pan and Tilt CCTV Control
------------------------	--

Coax Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax	Insulation Material	Insulation Nominal Diameter
18	Solid	BC - Bare Copper	0.032 in	1	Gas-injected FHDPE - Foam High Density Polyethylene	0.145 in

Coax Insulation

Insulation Material	Insulation Nominal Diameter
Gas-injected FHDPE - Foam High Density Polyethylene	0.145 in

Coax Outer Shield

Element	Outer Shield Type	Outer Shield Material	Outer Shield Coverage
1	Braid	BC - Bare Copper	90 %

Coax Outer Jacket

Outer Jacket Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.232 in

Coax High Frequency (Nominal Typical)

Frequency	Nominal Insertion Loss (Attenuation)
1 MHz	0.3 dB/100ft
5 MHz	0.65 dB/100ft
10 MHz	0.9 dB/100ft
50 MHz	1.9 dB/100ft
100 MHz	2.6 dB/100ft
200 MHz	3.6 dB/100ft
400 MHz	5.0 dB/100ft
700 MHz	7.0 dB/100ft
900 MHz	8.0 dB/100ft
1000 MHz	8.5 dB/100ft

Multiconductor

Multiconductor Conductor

No. of Pairs	AWG	Stranding	Material	Nominal Diameter
1	18	7x26	BC - Bare Copper	0.046 in

Multiconductor Insulation

Material
PP - Polypropylene
0.059 in

Multiconductor Color Chart

Description	Color
1	Black
2	Red

Shielding:	Braid(s)
------------	----------

Overall Cable

Jacket:	PVC
Operating Temp Range:	-30°C To +75°C
UL Temp Rating:	75°C
Max Recommended Pulling Tension:	75 lbs
Bulk Cable Weight:	50 lbs/1000ft

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU CE Mark:	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
China RoHS 2:	Yes

Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only
Suitability - Sunlight Resistance:	Yes - Black only
Below Grade Burial:	No

Flame Test

UL Flammability:	UL1685 UL Loading
C(UL) Flammability:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	649948

Product Notes

Notes:	18 AWG pair is unshielded
--------	---------------------------

Overall Armor Shield

Variants

Item #	Color	Footnote
549945 0101000	Black	C
549945 010500	Black	C
549945 0091000	White	C
549945 009500	White	C

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.