

**Industrial Ethernet
IE-XM-RJ45/RJ45**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Mounting rail outlet, RJ45 junction design according to IEC 60603-7-51

General ordering data

Type	IE-XM-RJ45/RJ45
Order No.	8879050000
Version	Terminal rail outlet, RJ45-RJ45 coupler, IP 20, Cat.6 (ISO/IEC 11801)
GTIN (EAN)	4032248614844
Qty.	1 pc(s).

Industrial Ethernet IE-XM-RJ45/RJ45

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 49 g

Temperatures

Operating temperature -25 °C...70 °C Storage temperature
 Installation temperature

Downloads

GL Approval Guidelines GL_Certificate.pdf GOST Approval POCC
 DE.ME25.B01411.pdf

General data

Category	Cat.6 (ISO/IEC 11801)	Colour	Light Grey
Configuration	Inspection window for labelling 1 TE pitch dimension acc. to DIN 43880. insta-compatible	Connection 1	
Connection 2	RJ45	Description of article	RJ45
Housing main material	PA 66, UL 94: V-0	Plugging cycles	RJ45-RJ45 coupler 750
Protection degree	IP 20	Type of mounting	TS 35
Wiring	Colour-coded pin assignment acc. to EIA/TIA T568 A (copper)		

Electrical properties

Contact resistance	≤ 20 mΩ	Current-carrying capacity at 50 °C	1 A
Dielectric strength, contact / contact	≥ 1000 V DC	Dielectric strength, contact / shield	≥ 1500 V DC
Insulation resistance	500 MΩ	PoE / PoE+	conforming to IEEE 802.3at

Standards

Connector standard IEC 60603-7-5 Certificate No. (GERMLLOYD) 33451-06
 Certificate no. (cULus) E316369

Classifications

ETIM 3.0 EC001264 UNSPSC 43-17-27-10
 eClass 5.1 27-25-05-04 eClass 6.2 27-25-05-04
 eClass 7.1 27-25-05-04

Approvals

Approvals



ROHS Conform

**Industrial Ethernet
IE-XM-RJ45/RJ45**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen**Dimensioned drawing**