

SIPLUS NET SCALANCE X202-2P IRT based on 6GK5202-2BH10-2BA3 with conformal coating, -40...+60 °C, managed IE IRT switch, 2x 10/100 Mbps RJ45 ports, 2x 100 Mbps POF SC RJ ports, error signaling contact with set pushbutton, redundant power supply, PROFINET IO device, network management, redundancy manager integrated, including electronic manual on CD C-PLUG optional

product type designation	
product brand name	SIPLUS
product type designation	X202-2P IRT
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections • for network components or terminal equipment	2
number of 100 Mbit/s SC-RJ-ports / for POF FOC / with push-pull connection system	2
interfaces / other	
number of electrical connections • for signaling contact • for power supply	1 1
type of electrical connection • for signaling contact • for power supply	2-pole terminal block 4-pole terminal block
design of the removable storage • C-PLUG	Yes
operating voltage / of the signaling contacts • at DC / rated value	24 V
operational current / of the signaling contacts • at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
type of voltage / 1 / of the supply voltage • supply voltage / 1 / rated value • power loss [W] / 1 / rated value • supply voltage / 1 / rated value • consumed current / 1 / maximum • product component / 1 / fusing at power supply input • fuse protection type / 1 / at input for supply voltage	DC 24 V 4.8 W 18 ... 32 V 0.2 A Yes 2.5 A (cannot be changed by user)
ambient conditions	
ambient temperature / in horizontal mounting position / during operation	-40 ... +60 °C
installation altitude / at height above sea level / maximum	5000 m
relative humidity • with condensation / according to IEC 60068-2-38 / maximum	100 %; RH including condensation/frost (no commissioning when condensation is present), horizontal installation
chemical resistance / to commercially available cooling lubricants	Yes; incl. airborne diesel and oil droplets
ambient condition / relating to ambient temperature - air pressure - installation altitude	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax - 20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
resistance to biologically active substances • conformity according to EN 60721-3-3 • conformity according to EN 60721-3-6	Yes; Class 3B2 mold and fungal spores (excluding fauna); class 3B3 on request Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)
resistance to chemically active substances • conformity according to EN 60721-3-3 • conformity according to EN 60721-3-6	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); * Yes; Class 6C3 (RH < 75%) incl. salt spray acc. to EN 60068-2-52 (Severity

	degree 3); *
resistance to mechanically active substances	
• conformity according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust; *
• conformity according to EN 60721-3-6	Yes; Class 6S3 incl. sand, dust; *
environmental category / according to IEC 60721 / note	* The supplied plug covers must remain in place on the unused interfaces during operation!
coating / for equipped printed circuit board / according to EN 61086	Yes; Class 2 for high availability
type of coating / protection against pollution according to EN 60664-3	Yes; protection of the type 1
type of test / of the coating / according to MIL-I-46058C	Yes; coating discoloration during service life possible
product conformity / of the coating / Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; conformal coating, class A
protection class IP	IP30
design, dimensions and weights	
design	compact
width	60 mm
height	125 mm
depth	124 mm
net weight	0.78 kg
fastening method	
• 35 mm DIN-rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of $\leq 0,31$-s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• port mirroring	No
• multiport mirroring	No
• with IRT / PROFINET IO switch	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
PROFINET conformity class	C
network load class / according to PROFINET	II
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes

<ul style="list-style-type: none"> • statistics Packet Size 	Yes
<ul style="list-style-type: none"> • statistics packet type 	Yes
<ul style="list-style-type: none"> • error statistics 	Yes
product functions / DHCP	
product function	
<ul style="list-style-type: none"> • DHCP client 	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • Media Redundancy Protocol for Planned Duplication (MRPD) 	Yes
<ul style="list-style-type: none"> • ring redundancy 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> • passive listening 	Yes
product functions / security	
protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes
product functions / time	
product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • NTP 	No
<ul style="list-style-type: none"> • SNTP 	Yes
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> • CE marking 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes
<ul style="list-style-type: none"> • Regulatory Compliance Mark (RCM) 	Yes
standard	
<ul style="list-style-type: none"> • for EMC interference emission 	EN 61000-6-4:2001 (Class A)
<ul style="list-style-type: none"> • for immunity to EMC 	EN 61000-6-4:2001
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 60950-1, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
<ul style="list-style-type: none"> • ATEX 	Yes
<ul style="list-style-type: none"> • UKEX 	Yes
<ul style="list-style-type: none"> • IECEx 	Yes
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard 	Yes
<ul style="list-style-type: none"> • FM registration 	Yes
standards, specifications, approvals / other	
certificate of suitability	
<ul style="list-style-type: none"> • railway application in accordance with EN 50155 	No
<ul style="list-style-type: none"> • railway application in accordance with EN 50124-1 	No
<ul style="list-style-type: none"> • RoHS conformity 	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
<ul style="list-style-type: none"> • total 	179.66 kg
<ul style="list-style-type: none"> • during manufacturing 	29.12 kg
<ul style="list-style-type: none"> • during operation 	150.31 kg
<ul style="list-style-type: none"> • after end of life 	0.23 kg

product functions / general	
MTBF	83.72 a
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 • according to IEC 81346-2:2019 	KF KFE
Warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022

further information / internet links	
internet link	
<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support 	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com

security information	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>

Approvals / Certificates	
General Product Approval	Environment

[Miscellaneous](#)

[Manufacturer Declaration](#)



last modified:

5/31/2025