



ENGLISH

Datasheet

Stock No: 458-904

RS Pro Crimp Tool, Crimp Contact, 0.22 → 0.35 mm², 0.8 → 0.22 mm² Wire Size



Product Details

'D' Connector Crimp Contact Tool

Suitable crimp tool having a small and large cavity to crimp pin or socket contacts suitable for 0.08-0.22 mm² and 0.22-0.35 mm² stranded wires.,ITT extraction tool also available.

Note

The current rating is with respect to 20awg wire. The crimp tool is not manufactured by ITT.

ITT D Type Connectors

Suitable for military, industrial or commercial applications and computer interfacing etc.

| | |
|------------------------------|---------------------------|
| | ITT D* U |
| | (crimp contacts) |
| Body | Steel |
| Surface, body (standard) | Yellow Chromate over Zinc |
| Insulator | Thermo Plastic |
| Insulation | UL94V0 |
| Contacts | Copper Alloy |
| Contact Plating: | Gold |
| Switch Current | 5A |
| Working Voltage | 400V= or ~ peak-peak |
| Contact Resistance (max) | 8mΩ |
| Insulation Resistance (min) | 5000mΩ |
| Temperature Range | -55°C to 125°C |
| Environmental Classification | - |
| No. of joints (min) | 500 |



ENGLISH

Specifications:

| | |
|-------------------|--|
| Connector Type | Crimp Contact |
| Wire Size | 0.22 → 0.35 mm ² , 0.8 → 0.22 mm ² |
| Minimum Wire Size | 0.8mm ² |
| Maximum Wire Size | 0.35mm ² |