


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**XT130B1PCM12**



Telemecanique Sensors  
 1875 Founders Drive  
 Dayton, OH 45420-4017  
 Customer Care Center : 1-800-435-2121  
 Web : [www.tesensors.com](http://www.tesensors.com)

**Technical Information:**

Max Range Adj:	10.0 mm (0.394 in)
Circuit Type:	NO + NC
Output Mode:	PNP
Volts Type:	DC
Voltage Range:	12-30 VDC
Max Load :	200 mA
Shielded:	Shielded
Operating Frequency:	150 Hz
Temp Range:	-25° to 70° C (-13° to 158° F)
NEMA Type:	4X (indoor use only)
Standards:	UL, CE Rohs

**Specification:**

Sensor Type:	Capacitive Sensor
Description:	Proximity Sensor, Capacitive, 30 mm Barrel, 12-30 VDC, Shielded
Body Style:	Barrel
Diameter:	mm
Face Material:	PBT Plastic
Housing Material:	Nickel Plated Brass
Cable Length:	
Connector Type:	M12
Special Features:	NO + NC outputs