

TECHNICAL DATA SHEET

Update of the document : 27-02-19
ISO reference of the document: DON/LS 03.4318.A



LEMAITRE SECURITE SAS
17 rue Bitschhoffen
CS 90024
F 67350 La Walck FRANCE
Tél. : +33 (0)3 88 72 28 80
Fax : +33 (0)3 88 07 05 37
www.lemaitre-securite.com
info@lemaitre-securite.com



CARIBU FEMME S2

High shoe in water-repellent
white microfiber

PROTECTIONS FOR THIS MODEL



EN ISO 20345 : 2011

Available sizes : from 35 (2) to 42 (8)
Poids par paire taille 37 : 780 gr.

Upper features

- Upper : water-repellent white microfiber
- Lining : three-dimensional textile
- Vamp lining : synthetic
- Backpart : synderm
- Tongue markings : size, manufacturer, manufacture date (month, year), norm, protection.

Protections 100% NON-METALLIC

- Toecap : HDFC Fiber composite (200 joules)

Fitting features

- Lasting insole : texon
- Footbed : foam and polyurethane

Sole features

- Name : PARABOLIGHT
- Material : dual density polyurethane
- Comfort sole density : 0,5
- Comfort sole color : white
- Outsole density : 1
- Outsole color : blue
- Slip resistance SRA (flat) : 0,33 ; (heel) : 0,36
- Slip resistance SRB (flat) : 0,23 ; (talon) : 0,21

Avantages = Bénéfices utilisateurs

100% Non-metallic shoe with a well fitting adapted to the morphology of the female foot. (MEDIUM size)

- ➔ **Water-repellent microfiber** : resistant, long life for the finished shoe and it helps to fight against water infiltration.
- ➔ **Three-dimensional micro-porous textile as lining** : High breathability thanks to its structure that allows better ventilation of sweat. It is flexible and it improves comfort.
- ➔ **HDFC (High Durability Fiber Composite) toecap** : non-metallic, non-magnetic, no heat or cold conduction.
- ➔ **PARABOLIGHT sole** :
 - ✓ **Slip resistant** sole thanks to a structured drawing "winter tire" design, which allows a quick evacuation of liquids.
 - ✓ **Special design to suit the shape of women's feet for a better fit.**
 - ✓ Polyurethane Double Density (PU2D) injected : **the best dual density** polyurethanes for the insole and outsole.
- ➔ **PARABOLIC® sole** :
 - ✓ **Exceptional grip** : the concave structure of the sole allows progressive bending of the sole in order to optimize grip.
 - ✓ **Comfort when walking** : the spring effect gives a more dynamic walk and facilitates walking.
 - ✓ **Anti-fatigue** : with every step, the recycled energy gives you a spring in your step and provides anti-fatigue effect to your legs.

Basics and additional requirements of the norm EN ISO 20345 : 2011

Toecap

steel polycarbonate aluminium HDFC Fiber composite

- A** Antistatic footwear.
- P** Penetration resistance.
- Hro** Resistance of the outsole to hot contact.
- Wru** Water penetration and water absorption resistant upper.
- E** Energy absorption of seat region.
- Hi** Heat insulation of sole complex.
- M** Metatarsal protection.

Anti-perforation insert

stainless steel composite (high tenacity fabric)

- Fo** Resistance of the outsole to fuel oil.
- Ci** Cold insulation of sole complex.
- Wr** Water resistant footwear.

Regarding the norm EN ISO 20345, the minimum results for slip resistance to get the SRC certificate are :
SRA (flat) ≥ 0,32 SRB (flat) ≥ 0,18
SRA (heel) ≥ 0,28 SRB (heel) ≥ 0,13



=

+

