



TE Internal #: 2-967650-1
Housing for Female Terminals, Wire-to-Wire, 7 Position, .449 in [11.4 mm] Centerline, Sealable, Gray, -40 – 248 °F [-40 – 120 °C], Key B
[View on TE.com >](#)

Connectors > Automotive Connectors > Connector Housings > CIRCULAR DIN HOUSINGS



Connector & Housing Type: **Housing for Female Terminals**
Mating Pin Diameter: **1.5 mm [.059 in]**
Connector System: **Wire-to-Wire**
Number of Positions: **7**
Centerline (Pitch): **11.4 mm [.449 in]**

[All CIRCULAR DIN HOUSINGS \(51\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	7
---------------------	---

Electrical Characteristics

Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V
------------------------------	------------------------

Body Features

Cable Exit Angle	180°
Body Material	Other
Primary Product Color	Gray



Connector Code	B
----------------	---

Contact Features

Mating Pin Diameter	1.5 mm[.059 in]
---------------------	-----------------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	No

Housing Features

Centerline (Pitch)	11.4 mm[.449 in]
--------------------	------------------

Dimensions

Product Length	31 mm[1.22 in]
Product Height	32.8 mm[1.291 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Industry Standards

Degree of Protection	IP69K
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Quantity	500
Packaging Method	Box

Other

Serviceable	No
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold










EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer











This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 828922-1 2,5MM CAVITY PLUG FOR 5,4MM DI</p>	 <p>TE Part # 828904-1 SINGLE WIRE SEAL FOR J.P.T.CON</p>	 <p>TE Part # CAT-C4962-B128 CIRCULAR DIN BACKSHELLS</p>	 <p>TE Part # CAT-R7602-T273 ROUND CONNECTOR SYSTEM, PIN AND SOCKET</p>
 <p>TE Part # 2-1718230-1 1,5MM PIN HSG 5-7 POS ASSY</p>	 <p>TE Part # 185636-1 PROTECT CAP 2.5MM PLUG</p>	 <p>TE Part # 185792-1 180 DEG CAP FOR CORRUGTD TUBE</p>	

Customers Also Bought



 <p>TE Part #1927574004 ATUM-6/2-2-SP</p>	 <p>TE Part #1-1718492-4 1.5MM TAB HSG 36 POS ASSY</p>	 <p>TE Part #HC5981 SCREW M6 x 20mm HEX HEAD CAPTIVE BATTER</p>	 <p>TE Part #927357-2 FF 110 2P HOUSING PA66 BLACK</p>
 <p>TE Part #4937914001 FRAG-18/10-0-SP</p>	 <p>TE Part #1-2278597-1 JPT REC. HSG, 8POSN.</p>	 <p>TE Part #2-2289748-0 58POS, MIXED, REC HSG, ASSY</p>	 <p>TE Part #2306928-1 16POS, MT 3, REC HSG ASSY</p>
 <p>TE Part #2359941-3 96POS, MCON-1.2 CB, REC HSG, ASSY</p>	 <p>TE Part #3-967624-6 JUN-POW-TIM GEH 18P</p>		

Documents

Product Drawings
1.5MM BU-STE KPL 7P

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_2-967650-1_G_c-2-967650-1-g.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_2-967650-1_G_c-2-967650-1-g.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_2-967650-1_G_c-2-967650-1-g.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

2-967650-1

Housing for Female Terminals, Wire-to-Wire, 7 Position, .449 in [11.4 mm] Centerline,
Sealable, Gray, -40 – 248 °F [-40 – 120 °C], Key B



Product Specification

English