



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Ferrule**

Primary Product Material: **Copper**

Number of Positions: **6**

Packaging Method: **Bulk**

Packaging Quantity: **1**

Features

Product Type Features

|                              |         |
|------------------------------|---------|
| Strain Relief Accessory Type | Ferrule |
|------------------------------|---------|

Configuration Features

|                     |   |
|---------------------|---|
| Number of Positions | 6 |
|---------------------|---|

Body Features

|                                  |        |
|----------------------------------|--------|
| Primary Product Plating Material | Tin    |
| Primary Product Material         | Copper |

Dimensions

|                                 |                                |
|---------------------------------|--------------------------------|
| Compatible Cable Diameter Range | 5.36 – 5.73 mm[.211 – .225 in] |
|---------------------------------|--------------------------------|

Industry Standards

|                                           |         |
|-------------------------------------------|---------|
| Compatible With Agency/Standards Products | CSA, UL |
|-------------------------------------------|---------|

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Method   | Bulk |
| Packaging Quantity | 1    |



Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Customers Also Bought



TE Part #207473-1  
CABLE CLAMP KIT,SZ 4



TE Part #206803-2  
AMPLIMATE RECEPT ASY,37 POS,



TE Part #206795-3  
AMPLIMATE,SKT CONT ASY,SZ 20



TE Part #8-323914-1  
TERMINAL,PIDG R 26-22 4




TE Part #323199  
DG 22-16COM 22-18MIL HR R 6



TE Part #2-329941-3  
TWIN THREADED RECPT




TE Part #6635996003  
LSTT-R-1.6-0



TE Part #520464-1  
8 SDL RND SHIELD,TOP,BULK PKG



TE Part #173977-5  
CT CONN MT REC ASSY 5P



TE Part #520463-1  
6 SDL RND SHIELD,BTTM,BULK PKG

Documents

Product Drawings  
6 SDL FERRULE,BULK PKG

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_520435-1\_L.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_520435-1\_L.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_520435-1\_L.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English