

HONEYWELL MILLER MB ENERGY ABSORBING LANYARD ROPE

Highly resistant, durable, lightweight – offers optimal protection and better comfort in case of fall.

FEATURES & BENEFITS

- Lightweight, anti-corrosion dachrotized steel connectors: double-lock scaffold hook, large opening 52mm; auto-twist locking carabiner, opening 17mm.
- Durable polyester rope Ø 12mm, static strength > 22 kN.
- Energy Absorber, high resistant 32mm polyamide double-layer tearing webbing.
- Maximum arresting force of 6kN.

REF.	SINGLE/TWIN TAILS	CONNECTORS	NET WEIGHT
MB9006	Single Tail Lanyard Rope	1 Double-lock Scaffold Hook, 1 Auto-twist Locking Carabiner	850g
MB9007	Twin Tails Lanyard Rope	1 Double-lock Scaffold Hook, 2 Auto-twist Locking Carabiner	1.79kg



Ref. MB9006



Ref. MB9007



CERTIFICATIONS

- EN 355:2004
- Singapore PSB SS528: Part 6: 2006
- Malaysia SIRIM



APPLICATION

Suitable for fall arrest application in construction industry and for general works at height.

For more information

www.honeywellsafety.com

Honeywell Personal Protective Equipment

Malaysia (Asia Pacific Headquarters)

Level 25, UOA Corporate Tower,
Lobby B, The Vertical, Bangsar South
City, 59200 Kuala Lumpur, Malaysia

Phone: +603-2777 3948 / 3950

Email: hsp.asean@Honeywell.com

Singapore: +65 6714 6800

Indonesia: +62 21 2964 0328

Philippines: +632 730 7300

Thailand: +66 2 693 3099

Vietnam: +84 28 5411 2260

Harness-DS | Rev01 | 11/20
© 2020 Honeywell International Inc.

THE
FUTURE
IS
WHAT
WE
MAKE IT

Honeywell