



GCSV-028 SILICONE INTERFACE MATERIAL

GCSV-028 Silicone Based Thermal Interface Material

Features

- 2.8 W/m K thermal conductivity
- High resistance to puncture, shear, and tearing
- Soft and conformable for optimal contact
- Excellent electrical insulation



Configurations

PART NUMBER	TOTAL THICKNESS (MM)
GCSV-028-200-0.5	0.5
GCSV-028-200-1.0	1
GCSV-028-200-1.5	1.5
GCSV-028-200-2.0	2
GCSV-028-200-3.0	3

Properties

CHARACTERISTIC	TEST METHOD	VALUE
Colour	Visual	White and Pink
Thickness mm		0.5 to 3
Thermal conductivity W/m*K	ASTMD5470	2.8
Hardness (shore OO)	ASTMD2240	30±5
Specific gravity. g/cm3	ASTMD792	2.85±0.1
Compression rate	ASTM D412	30
Volume resistance	ASTM D257	1.0*10 ¹¹
Operation temperature (°C)	EN344	-40~150
Flame rating	UL94	V-0



✉ info@gcsthermal.com

GCS UK Ltd
7 Priory Business Park
Kibworth, Leicestershire
LE8 0RX, UK