
KEMET Part Number: C0805C683KARACAUTO



SMD Auto X7R, Ceramic, 0.068 uF, 10%, 250 VDC, X7R, SMD, MLCC, Temperature Stable, Automotive Grade, 0805



Dimensions	
L	2mm +/-0.2mm
W	1.25mm +/-0.2mm
Т	1.25mm +/-0.15mm
S	0.75mm MIN
В	0.5mm +/-0.25mm

Packaging Specifications		
Packaging:	T&R, 180mm, Plastic Tape	
Packaging Quantity:	2500	

General Information		
Supplier:	KEMET	
Series:	SMD Auto X7R	
Style:	SMD Chip	
Description:	SMD, MLCC, Temperature Stable, Automotive Grade	
Features:	Temperature Stable, Automotive Grade	
RoHS:	Yes	
Termination:	Tin	
Marking:	No	
Qualifications:	AEC-Q200	
AEC-Q200:	Yes	
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours	
Chip Size:	0805	
Shelf Life:	78 Weeks	
MSL:	1	

Specifications		
Capacitance:	0.068 uF	
Capacitance Tolerance:	10%	
Voltage DC:	250 VDC	
Dielectric Withstanding Voltage:	625 VDC	
Temperature Range:	-55/+125°C	
Temperature Coefficient:	X7R	
Dissipation Factor:	2.50% 1kHz 25C	
Aging Rate:	3% Loss/Decade Hour	
Insulation Resistance:	1.471 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

