



Technical data

4T-JM716648/JM716610PK

Single row tapered roller bearings

Tapered roller bearing, pressed steel cage

KIT CONTENT


4T-JM716648PK

VISUAL (S)



4T-JM716648/JM716610PK

Single row tapered roller bearings



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	85 mm
D - External diameter	130 mm
B - Bearing/Inner ring width	29 mm
C - Outer ring width	24 mm
T - Total width	30 mm
a - Charge load application point	29,8 mm
rs - Min fillet radius	6 mm
r1s - Min fillet radius	2,5 mm
Mass	1,37 kg

PRODUCT PERFORMANCE	
C - Dynamic load	149 kN
C0 - Static load	214 kN

4T-JM716648/JM716610PK

Single row tapered roller bearings

PRODUCT PERFORMANCE

A2 - Rating life coefficient	1
e - Coefficient	0.44
Y0 - Static axial load coefficient	0.74
Y2 - Upper axial load coefficient	1.35
N lim - Oil lubrication limit speed	3500 tr/min
N lim - Grease lubrication limit speed	2600 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	92 mm
db min - Min IR shoulder diameter	104 mm
Da max - Max shoulder diameter OR	125 mm
Db min - Min OR shoulder diameter	207 mm
ra max - Max fillet radius	6 mm
r1a - Max fillet radius	2,5 mm

KIT COMPONENT

Cone designation	4T-JM716648PK
------------------	---------------

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-JM716648/JM716610PK
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No
Rolling element material	Acier de cémentation



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

X_0	Y_0
0.5	Y0

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y2 and Y0 are shown in the above table

