

# Product datasheet

Specifications



## servo motor MH3 070 2,2Nm, no key, multi, brake, IP65/IP67, 6kRPM

MH30702P02F2200

⚠ Discontinued on: 9 Feb 2023

EAN Code: 3606485395166

⚠ Discontinued

### Main

Range compatibility	PacDrive 3
Device short name	MH3
Product or component type	Servo motor

### Complementary

Maximum mechanical speed	8000 rpm
[Us] rated supply voltage	115...480 V
Network number of phases	Three phase
Continuous stall current	2.94 A
Continuous stall torque	2.48 N.m, 115...480 V, three phase
Continuous power	1380 W
Peak stall torque	7.4 N.m, 115...480 V, three phase
Nominal output power	0.31 W, 115 V 0.7 W, 230 V 1.16 W, 400 V 1.38 W, 480 V
Nominal torque	2.37 N.m for LXM52 at 2.82 mA, 115 V, three phase 2.23 N.m for LXM52 at 2.7 mA, 230 V, single phase 2.01 N.m for LXM52 at 2.49 mA, 400 V, three phase 1.89 N.m for LXM52 at 2.36 mA, 480 V, three phase 2.37 N.m for LXM62 at 2.82 mA, 115 V, single phase 2.23 N.m for LXM62 at 2.7 mA, 230 V, single phase 2.01 N.m for LXM62 at 2.49 mA, 400 V, three phase 1.89 N.m for LXM62 at 2.36 mA, 480 V, three phase
Nominal speed	1250 rpm for LXM52 at 2.82 mA, 115 V, single phase 3000 rpm for LXM52 at 2.7 mA, 230 V, single phase 5500 rpm for LXM52 at 2.49 mA, 400 V, three phase 7000 rpm for LXM52 at 2.36 mA, 480 V, three phase 1250 rpm for LXM62 at 2.82 mA, 115 V, single phase 3000 rpm for LXM62 at 2.7 mA, 230 V, single phase 5500 rpm for LXM62 at 2.49 mA, 400 V, three phase 7000 rpm for LXM62 at 2.36 mA, 480 V, three phase
Maximum current Irms	9.65 A
Shaft end	Smooth shaft
Second shaft	Without second shaft end
Shaft diameter	11 mm
Shaft length	23 mm
IP degree of protection	IP65 standard

<b>Encoder type</b>	Multiturn SinCos Hiperface
<b>Speed feedback resolution</b>	128 periods
<b>Holding brake</b>	With
<b>Holding torque</b>	3 N.m
<b>Mounting support</b>	International standard flange
<b>Motor flange size</b>	70 mm
<b>Electrical connection</b>	Rotatable right-angled connectors
<b>Torque constant</b>	0.84 N.m/A at 120 °C
<b>Back emf constant</b>	54.08 V/krpm
<b>Number of motor poles</b>	5.0
<b>Rotor inertia</b>	1.24 kg.cm <sup>2</sup>
<b>Stator resistance</b>	3.84 Ohm
<b>Stator inductance</b>	12.19 mH
<b>Stator electrical time constant</b>	3.2 ms
<b>Maximum radial force Fr</b>	710 N at 1000 rpm 560 N at 2000 rpm 490 N at 3000 rpm 450 N at 4000 rpm 410 N at 5000 rpm 390 N at 6000 rpm
<b>Brake pull-in power</b>	7 W
<b>type of cooling</b>	Natural convection
<b>Length</b>	193 mm
<b>Centring collar diameter</b>	60 mm
<b>centring collar depth</b>	2.5 mm
<b>Number of mounting holes</b>	4
<b>Mounting holes diameter</b>	5.5 mm
<b>Circle diameter of the mounting holes</b>	82 mm
<b>Net weight</b>	3.3 kg
<b>Sizing reference</b>	MH30702P
<b>Temperature copper hot</b>	135 °C
<b>compatible drive output current 3s peak 2</b>	15 A

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	11.5 cm
<b>Package 1 Width</b>	19.0 cm
<b>Package 1 Length</b>	39.5 cm
<b>Package 1 Weight</b>	2.3 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) **1320**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

REACH Regulation [REACH Declaration](#)

PVC free **Yes**

## Use Again

### Repack and remanufacture

Circularity Profile **No need of specific recycling operations**

Take-back **No**

WEEE  **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**