


## TT-UK5/ 24DC

Order No.: 2794699



Modular terminal block with surge voltage fine protection between clamping connector and DIN rail, nominal voltage: 24 V DC, for mounting on NS 32 or NS 35/7.5, terminal width: 6.2 mm, terminal height: 47 mm

### Commercial data

EAN	 4 017918 072872
Pack	50
Customs tariff	85363030
Country of Origin	GR
Catalog page information	Page 111 (TT-2011)

### Product notes

WEEE/RoHS-compliant since:  
31/01/2006



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### General

Housing material	PA
Inflammability class according to UL 94	V2
Color	black

Total surge current (8/20) $\mu$ s	169 A
Ambient temperature (operation)	-40 °C ... 85 °C
Mounting type	DIN rail/G-profile rail
Design	Single-level terminal block
Number of positions	1
Degree of protection	IP20
Direction of action	Line-Earth Ground
Width	6.20 mm
Height	47.00 mm
Length	42.50 mm

#### Protective circuit

IEC category	C3
VDE requirement class	C3
Nominal voltage $U_N$	24 V DC
Maximum continuous operating voltage $U_C$	28 V DC
	20 V AC
Maximum continuous voltage $U_C$ (wire-ground)	28 V DC
	20 V AC
Nominal current $I_N$	32 A (50°C)
Ground conductor current $I_{PE}$	$\leq 5 \mu$ A
Nominal discharge surge current $I_n$ (8/20) $\mu$ s (Core-Earth)	169 A
Total surge current (8/20) $\mu$ s	169 A
Max. discharge surge current $I_{max}$ (8/20) $\mu$ s maximum (Core-Earth)	169 A
Nominal pulse current $I_{an}$ (10/1000) $\mu$ s (Core-Earth)	33 A
Output voltage limitation at 1 kV/ $\mu$ s (Core-Earth) spike	$\leq 40$ V
Output voltage limitation at 1 kV/ $\mu$ s (Core-Earth) static	$\leq 40$ V
Residual voltage at $I_n$ , (conductor-ground)	$\leq 55$ V
Response time $t_A$ (Core-Earth)	$\leq 1$ ns
Cut-off frequency $f_g$ (3 dB), asym. (PE) in 150 Ohm system	Typ. 1.2 MHz
Capacity (Core-Earth)	$\leq 1.35$ nF
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C3 (25 A)

---

**Connection data**

Connection method	Screw connection
Connection type IN	Screw terminal blocks
Connection type OUT	Screw terminal blocks
Screw thread	M3
Tightening torque	0.5 Nm
Stripping length	8 mm
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	4 mm <sup>2</sup>
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

**Connection, protective circuit**

Standards/regulations	IEC 61643-21
-----------------------	--------------

**Certificates**

Certification

CSA, CUL, GOST, UL

---

**Accessories**

Item	Designation	Description
------	-------------	-------------

**Assembly**

2794990	D-TERMITRAB-UK 5	Cover for setting the end of a TT-UK 5 row of terminal blocks, color: black
---------	------------------	---

**Marking**

1051993	B-STIFT	Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm
1051016	ZB 6,LGS:FORTL.ZAHLEN	Zack marker strip, 10-section, printed horizontally: with the numbers 1 - 10, 11 - 20 and so on up to 491 - 500, color: white
1051414	ZB 6,LGS:L1-N,PE	Zack strip, printed horizontally, strips with 10 labels, L1, L2, L3, N, PE, L1, L2, L3, N, PE, color: white

---

1051430	ZB 6,LGS:U-N	Zack strip, printed horizontally: 10-section, U, V, W, N, GND, U, V, W, N, GND, color: white
1050499	ZB 6:SO/CMS	Zack strip, 10-section, divisible, special printing, marking according to customer requirements
1051003	ZB 6:UNBEDRUCKT	Zack strip, unprinted, strips with 10 labels for individual labeling with M-PEN or CMS system, for terminal block width: 6.2 mm, color: white
0808749	ZBF 6,LGS:FORTL.ZAHLEN	Zack marker strip, flat, printed horizontally: 10-section, with the numbers 1 - 10, 11 - 20, and so on up to 91 - 100, color: white
0808736	ZBF 6/WH-100:UNBEDRUCKT	Zack strip, flat, unprinted: 10-section, for individual labeling with M-PEN or ZBF-T, large batch, sufficient for labeling 1000 terminal blocks, color: white
0808710	ZBF 6:UNBEDRUCKT	Zack strip, flat, unprinted: 10-section, for individual labeling with M-PEN or ZBF-T, sufficient for 100 terminal blocks, color: white

### Additional products


Item	Designation	Description
------	-------------	-------------

### Assembly

2794990	D-TERMITRAB-UK 5	Cover for setting the end of a TT-UK 5 row of terminal blocks, color: black
2839295	SSA 3-6	shield fast connections for conductor diameter 3 - 6 mm. Potential connection cable: 200 mm, black
2839512	SSA 5-10	Shield fast connection for conductor diameters 5 - 10 mm. Potential connection cable: 200 mm, black

### Drawings

Circuit diagram



---

Schematic diagram

---

