



PRODUCT-DETAILS

K6-22Z-F-03

K6-22Z-F-03Mini Contactor Relay48 V AC2NO2NCFlat-Pin Connections



General Information

Extended Product Type	K6-22Z-F-03
Product ID	GJH1211003R0223
EAN	4013614231339
Catalog Description	K6-22Z-F-03Mini Contactor Relay48 V AC2NO2NCFlat-Pin Connections
Long Description	The K6-22Z-F mini contactor relay is a compact 4 pole contactor relay with flat pin connection. They are ideally suited for applications where reliability is a must and space is at a premium. Mini contactors relays are used in residential buldings, commercial buildings and industrial applications for switching of control signals up to 3 A / 400 V (AC-15). Further features are the silent coil, a switch position indication and the integrated possibility for rail or wall mounting.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080

Popular Downloads

EPLAN Data	9AAC202719_EPLAN
Data Sheet, Technical	1SBC100214C0202

Information

Instructions and Manuals	2CDC102047M6801
CAD Dimensional Drawing	2CDC001079B0201

Dimensions

Product Net Width	52.5 mm
Product Net Depth / Length	46.5 mm
Product Net Height	57.5 mm
Product Net Weight	0.17 kg
Dimension Diagram	GJL1200437F0001

Technical

Number of Main Contacts NO	0
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	2
Number of Auxiliary Contacts NC	2
Number of Poles	4P
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1 IEC 60335-2-40 A2L
Rated Operational Voltage	Auxiliary Circuit 690 V AC Auxiliary Circuit 250 V DC
Rated Frequency (f)	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Auxiliary Circuit DC Control Circuit 400 Hz Control Circuit 50 Hz Control Circuit 60 Hz Main Circuit 60 Hz Main Circuit 50 Hz Main Circuit DC
Conventional Free-air Thermal Current (I_{th})	Auxiliary Circuit 6 A
Rated Operational Current AC-15 (I_e)	(24 V) 4 A (120 V) 4 A (240 V) 4 A (400 V) 3 A (500 V) 2 A
Rated Operational Current DC-13 (I_e)	(24 V) 2.5 A (110 V) 0.7 A (220 / 240 V) 0.4 A
Short-Circuit Protective Devices	gG Type Fuses 6 A
Rated Insulation Voltage (U_i)	690 V acc. to UL/CSA 600 V
Rated Impulse Withstand Voltage (U_{imp})	Auxiliary Circuit 6 kV
Maximum Electrical Switching Frequency	(AC-15) 600 cycles per hour (DC-13) 600 cycles per hour
Mechanical Durability	Nr. Operations 10000000 cycle
Minimum Switching Capacity	17 V 5 mA
Coil Operating Limits	(acc. to IEC 60947-5-1) for AC supply 0.85 ... 1.1 x U_c (at $\theta \leq 55^\circ\text{C}$)
Rated Control Circuit Voltage (U_c)	48 V AC

Coil Consumption	Average Holding Value 50 Hz 3.5 V·A Average Pull-in Value 50 Hz 3.5 V·A
Power Loss	at Rated Operating Conditions per Pole 0.32 W
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Degree of Protection	Auxiliary Circuit Terminals IP20 Control Circuit Terminals IP20
Terminal Type	Flat-Pin Connections
Mini Contactor Type	Mini Contactor Relay
Product Name	Mini Contactor Relay

Technical UL/CSA

Maximum Operating Voltage UL/CSA	600 V AC
General Use Rating UL/CSA	(600 V AC) 5 A
Contact Rating UL/CSA	A600

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +80 °C
Maximum Operating Altitude Permissible	2000 m
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 15g
Resistance to Vibrations	3g 3 ... 150 Hz

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS Declaration	2CMT2021-006277
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

ABB EcoSolutions

End Of Life Disassembling Instructions	1SBC100156C0263
Environmental Product Declaration - EPD	1SAC200409H0001

Certificates and Declarations

A2L Certificate - IEC	1SAA938000-4601
CB Certificate	1SAA938001-2001
CQC Certificate	CQC2003010304064035
cURus Certificate	1SAA938000-1901
Declaration of Conformity - CCC	2020980304001309
Declaration of Conformity - CE	1SAD101100-3101

Declaration of Conformity - UKCA	1SAD201100-3101
EAC Certificate	1SAA938001-2701
RMRS Certificate	1SAA938001-0704
UL Certificate	E48139-19881213
UR Certificate	1SAA938000-1801

Container Information

Package Level 1 Units	box 10 piece
Package Level 1 Width	115 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 Height	54 mm
Package Level 1 Gross Weight	1.77 kg
Package Level 1 EAN	4013614410451

External Classifications and Standards

Object Classification Code	K
ETIM 7	EC000196 - Contactor relay
ETIM 8	EC000196 - Contactor relay
ETIM 9	EC000196 - Contactor relay
eClass	V11.0 : 27371001
UNSPSC	39121500

Categories

Low Voltage Products and Systems → Control Products → Contactors → Mini Contactor Relays

