

TSN 125

Torque wrench TSN SLIPPER

1-125 Nm / 10-1106 lbf·in / pre-set

Code ETIM
7092200 EC002132

EAN UNSPSC
4002805759035 27-11-17-15

Country of origin eCl@ss
Germany 21-04-02-22

Customs tariff number
82041100



Article description

- Use:
- Controlled screw tightening in the range of 40 - 125 Nm
- Serial / production-line
- Extremely long-term work
- Features:
- Pre-set torque wrench - without scale
- 1/2" square drive with ball lock
- With integrated ratchet-function for controlled clockwise tightening
- Working accuracy: +/- 4 % tolerance of set torque
- Acc. to DIN EN ISO 6789, traceable to national standards
- Precision mechanism slips very noticeably and audibly ("click") when the pre-set value is achieved - over-tightening is not possible
- Automatic resetting to the starting position
- Lightweight, but robust and corrosion-resistant construction design
- Very convenient non-slip rubber handgrip
- The pre-setting can be made at the factory or by the user on suitable torque testers
- If fixed setting at the factory is desired is required, please state the Nm value when ordering (price on request)
- EPA-conformant (Electrostatic Protected Area), for use in sensitive electrostatic applications
- Scope of delivery:
- Torque wrench type TSN SLIPPER
- Special adjusting key for changing the pre-set torque value
- Test certificate acc. to DIN EN ISO 6789
- Delivery in sturdy cardboard packaging

Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [N·m]	40 Nm - 125 Nm
Net weight [kg]	1,36 kg	Torque range (min./max.) [lbf·ft]	30 lbf·ft - 90 lbf·ft
Total length [mm]	460 mm	Epa-/Esd-Model	no
Drive connector square (male)	1/2"	Torque (max.) [lbf·in]	354 lbf·in
Drive connector square (male)	12,5 mm	Torque (min.) [lbf·in]	1106 lbf·in
Drive type/drive	Single square ratchet	Trigger mechanism	Friction clutch
Torque (min.) [N·m]	40 Nm	Precision +/-	+/- 4 %
Torque (max.) [N·m]	125 Nm	Direction of tightening	Right
Torque (min.) [lbf·ft]	30 lbf·ft	Fixed setting	yes
Torque (max.) [lbf·ft]	90 lbf·ft	Test certificate	DIN EN ISO 6789-2:2017