

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight bulkhead receptacle, jack (female)

22_BNC-50-0-4/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration

Interface type	Gender	Standard
BNC	jack	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data

Weight	0.008 kg
Mating cycles	500
Flange type	round flange / dia. 12.5
Tab style	solder end

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight bulkhead receptacle, jack (female)

22_BNC-50-0-4/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22540303	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22540303	22_BNC-50-0-4/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P50846 / Date of publication: 12.07.2025 / uncontrolled copy