


FEATURES

- **High-Quality Material:** Constructed from Fluorinated Ethylene Propylene and Viton for enhanced chemical resistance and durability
- **Wide Temperature Range:** Operates effectively from -20 °C to 140 °C, suitable for diverse environments
- **Precision Dimensions:** Inside diameter of 367.67 mm and outside diameter of 381.65 mm ensure a perfect fit
- **Optimal Hardness:** Shore A 90 to 95 provides a balance of flexibility and strength
- **Compliance with Standards:** Meets BS ISO 3601-1, AS 568, and other key standards for assured quality

RS PRO 367.67 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-540



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene and Viton, it ensures durability and resistance to extreme temperatures. Ideal for environments requiring robust sealing solutions, this O-Ring Seal offers excellent performance and longevity.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	367.67 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	381.65 mm
Thickness	6.99 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

