



Technical data

4T-21075/21212


Single row tapered roller bearings

Tapered roller bearing, pressed steel cage

KIT CONTENT

4T-21075, 4T-21212

VISUAL (S)



4T-21075/21212

Single row tapered roller bearings



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	19,05 mm
D - External diameter	53,975 mm
B - Bearing/Inner ring width	21,839 mm
C - Outer ring width	15,875 mm
T - Total width	22,225 mm
d1 - External diameter inner ring	36,2 mm
a - Charge load application point	16,625 mm
rs - Min fillet radius	1,5 mm
r1s - Min fillet radius	2,3 mm
Mass	0,248 kg

PRODUCT PERFORMANCE

C - Dynamic load	44,5 kN
------------------	---------



PRODUCT PERFORMANCE

C0 - Static load	39 kN
Cu - Fatigue limit load	4,75 kN
A2 - Rating life coefficient	1
e - Coefficient	0.59
Y0 - Static axial load coefficient	0.56
Y2 - Upper axial load coefficient	1.02
N lim - Oil lubrication limit speed	11000 tr/min
N lim - Grease lubrication limit speed	8000 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	26 mm
db min - Min IR shoulder diameter	31,5 mm
Da max - Max shoulder diameter OR	43 mm
Db min - Min OR shoulder diameter	50 mm
ra max - Max fillet radius	1,5 mm
r1a - Max fillet radius	2,3 mm

KIT COMPONENT

Cone designation	4T-21075
Cup designation	4T-21212

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-21075/21212



ESHOPDONOTDISPLAY

Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No
Rolling element material	Acier de cémentation

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
0.5	Y0

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y2 and Y0 are shown in the above table

