



MALE END VIEW






PIN-OUT DIAGRAM



SPECIFICATIONS

CONTACT CARRIER MATERIAL/COLOR	NYLON/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
HOUSING MATERIAL/PLATING	BRASS/NICKEL
NUMBER OF CONTACTS	4 x 0.025 IN SQ. POSTS
RATED CURRENT [A]	2.0 A
RATED VOLTAGE [V]	36 VDC
TEMPERATURE RANGE	-30°C to +105°C (-22°F to +221°F)
MAXIMUM PCB THICKNESS	1.6 MM [0.06 IN]
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67



SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 8-164-02 revP2 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
	MATERIAL	DRFT RDS DSGN GC	DATE 12/17/02 SCALE 4=1	DESCRIPTION WMFS 4F-PCB	
FINISH	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY  CONTACT TURCK FOR MORE INFORMATION	UNIT OF MEASUREMENT <b>MILLIMETER [ INCH ]</b>		IDENTIFICATION NO. U0902-44	REV E
E UPDATE CURRENT AND TEMP SPECS RDS 09/16/11 36501		DO NOT SCALE THIS DRAWING		FILE: U0902-44	SHEET 1 OF 1
REV DESCRIPTION	BY DATE ECO NO.				

E	UPDATE CURRENT AND TEMP SPECS	RDS	09/16/11	36501
REV	DESCRIPTION	BY	DATE	ECO NO.