

# CCT16652

IHP'cllic - intuitive switch - 2 channels - 7D 24 H  
- 6 years memory



## Main

Range of product	DuoLine
Modular device name	IHP'cllic
Modular device type	Intuitive switch
Number of channels	2
Battery type	Lithium
Modular device additional info	Absence for holidays function Automatic time changeover Mechanical compatibility with electrical distribution comb busbars Override controls On/Off

## Complementary

Cycle duration	7 days 24 hours
Bulb type	230 V AC halogen lamp 2300 W 230 V AC incandescent lamp 2300 W Dual mounted fluorescent tube conventional 10 2 x 58 W Dual mounted fluorescent tube conventional 5 2 x 100 W Dual mounted fluorescent tube electronic 5 2 x 36 W Dual mounted fluorescent tube electronic 3 2 x 58 W Fluocompact lamp electronic 9 7 W Fluocompact lamp electronic 7 11 W Fluocompact lamp electronic 7 15 W Fluocompact lamp electronic 7 20 W Fluorescent tube electronic 9 36 W Fluorescent tube electronic 6 58 W Non-corrected fluorescent tube 20 58 W Non-corrected fluorescent tube 10 100 W Non-corrected fluorescent tube 26 36 W Parallel-corrected fluorescent tube conventional 10 36 W Parallel-corrected fluorescent tube conventional 6 58 W Parallel-corrected fluorescent tube conventional 2 100 W Parallel-corrected mercury and sodium vapour lamps 250 W Serial-corrected fluorescent tube 26 36 W Serial-corrected fluorescent tube 20 58 W Serial-corrected fluorescent tube 10 100 W
Power consumption	8.5 VA
Maximum switching current	10 A 250 V AC 0.6 16 A 250 V AC 1
[Ue] rated operational voltage	230 V AC
Display type	LCD
Battery life	12 yr
Maximum number of switchings	42
Minimum interval duration	1 min
Backup time	6 years time and program saving
Product mounting	DIN rail
9 mm pitches	5
Connections - terminals	Screw terminal $\leq 6 \text{ mm}^2$
Product weight	0.16 kg

## Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP20 B