


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECN-24-247466	07OCT2024	DW	VK
	A1	REVISED PER ECN-24-288287	11OCT2024	DW	VK



 : RECOMMENDED LAND PATTERN


NOTES : UNLESS OTHERWISE SPECIFIED.

1. MATERIAL : CERAMIC
2. CONSULT TE CONNECTIVITY DATA SHEET : L000703

 .MARKING : INDICATION DIRECTION



4. CONTACT TE CONNECTIVITY ENGINEERING PRIOR TO DESIGNING INTO AN APPLICATION.
5. PACKAGING : TAPE AND REEL PACKAGED, SEE SHEET 2.

TAPE AND REELED	L000703-01
PACKAGING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW. PARK 13OCT2023		 TE Connectivity				
		CHK SJ. NOH 13OCT2023						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Chip ant, 1561-1602MHz, 3.05x1.6x0.55				
		APVD JH. KIM 13OCT2023		- -				
		PRODUCT SPEC -						
		APPLICATION SPEC -						
		WEIGHT -						
MATERIAL SEE NOTE 1 -		FINISH - -		SIZE A3	CAGE CODE 00779	DRAWING NO C-L000703	RESTRICTED TO -	
CUSTOMER DRAWING						SCALE 30:1	SHEET 1 OF 4	REV A1

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

AS SHOWN L000703-01
ANTENNA WITH REEL PACKAGING
REFERENCE ONLY



[FOR REFERENCE]DA PACKAGE


NOTES.

1. UNLESS OTHERWISE SPECIFIED TOLERANCE PER EIA-481-D

2 ORIENT PARTS AS SHOWN.

3 MATERIAL : P.S 0.4mm THICKNESS, COLOR : BLACK, CONDUCTIVE
WHEN ALTERNATIVEMATERIAL (PET, P.P) USE, CONSULT ECO PRIOR TO MANUFACTURER.


4. Q'TY/REEL : 5000PCS/REEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW.PARK	13OCT2023	 TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK SJ.NOH	13OCT2023		
		APVD JH.KIM	13OCT2023		
		PRODUCT SPEC	-		
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -	APPLICATION SPEC	-	NAME Chip ant, 1561-1602MHz, 3.05x1.6x0.55	
		WEIGHT	-	-	
MATERIAL SEE NOTE 3	-	CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779
-	-	SCALE 5:1		DRAWING NO C-L000703	RESTRICTED TO -
		SHEET 2 OF 4		REV A1	

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

SEE DETAIL B

AS SHOWN L000703-80
ANTENNA WITH EVB ASS'Y



NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL : SEE TABLE.
2. FINISH : EVB ASSEMBLY WITH SOLDER PROCESS

3. SILKSCREEN : WHITE EPOXY INK
A. TE LOGO, TE P/N
B. WORD REV., FOLLOWED BY THE LATEST REVISION, AS SHOWN/
C. 4 DIGITS DATE CODE : FIRST 2 DIGITS FOR THE WEEK CODE AND THE 2ND TWO DIGITS FOR THE YEAR CODE.
OTHERS : SPECIFIED TE SOURCE CODE NUMBER DIGITS AS REQUIRED.
4. CONSULTS TE CONNECTIVITY DATA SHEET L000703
 5. CONTACT TE CONNECTIVITY ENGINEERING PRIOR TO DESIGNING INTO AN APPLICATION.
 6. PACKAGING: SECURELY VACUUM PACKAGED IN BULK (REFER TO SHEET 4)


VACUUM IN BULK		L000703-80
PACKAGING		PART NUMBER
1	RESISTOR(00HM)	7
1	CAPACITOR(3.3pF)	6
1	CAPACITOR(1pF)	5
1	CAPACITOR(2pF)	4
1	SMA FEMALE CONNECTOR	3
1	EVB	2
1	L000703-01 ANTENNA	1
Q'TY (PC)	DESCRIPTION	ITEM

DETAIL B
SCALE 3:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW.PARK 13OCT2023	TE Connectivity NAME Chip ant, 1561-1602MHz, 3.05x1.6x0.55 - SIZE CAGE CODE DRAWING NO RESTRICTED TO A300779C-L000703		
DIMENSIONS: mm		CHK SJ.NOH 13OCT2023			
		APVD JH.KIM 13OCT2023			
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL SEE NOTE 1		WEIGHT			
		CUSTOMER DRAWING	SCALE 1:1	SHEET 3 OF 4	REV A1

PACKAGING SPECIFICATIONS
FOR REFERENCE


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



ANTENNA WITH EVB ASS'Y




IPC/BAG(BUBBLE WRAP)




10PCS/ZIPPER BAG




NOTES: IF PO Q'TY LESS THAN 120PCS,
WILL FILL THE OUTSIDE CARTON WITH PAPER (OR BUBBLE WRAP ETC.)
INSTEAD OF THE USING EMPTY BOX




4 ZIPPER BAGS/BOX
40PCS/BOX
BOX SIZE : 152x261x118(MM)



4 BOXES



4 BOXES/CARTON
160PCS/CARTON
SIZE : 330x280x254(MM)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW. PARK	13OCT2023	 TE Connectivity				
		CHK SJ. NOH	13OCT2023					
DIMENSIONS: mm		APVD JH. KIM	13OCT2023	NAME Chip ant, 1561-1602MHz, 3.05x1.6x0.55				
		PRODUCT SPEC -		SIZE A3		CAGE CODE 00779	DRAWING NO C-L000703	RESTRICTED TO -
		APPLICATION SPEC -						
		WEIGHT -						
		CUSTOMER DRAWING						
MATERIAL SEE NOTE 1 -		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		SCALE 1:1		SHEET 4 OF 4		REV A1