


PXM7011/02S/ST/1113/SN Datasheet



Product Name // Inline Cable Connector PXM7011 Series 2
Contact Socket Screw Termination (contacts supplied fitted) 11mm-13mm Cable (Yellow Gland) Metal Body With Braid Termination

[View Product Page](#)



// Product Description:	
- Inline Cable Connectors - Water and dustproof to IP66, IP68, IP69K when mated with compatible connector - Quick turn locking ring with less than quarter turn locking and positive feedback - Plug or Socket 2, 3, 6, 10, 32 Contact with leading Earth contact on 3 Contact versions - Screw, Crimp/Solder terminations available, depending on part code; Screw contacts supplied fitted, Crimp/Solder contacts and fitting tools available separately - Choice of body material depending on part code:	- Plastic body (part codes prefixed PXP) - Metal body (part codes prefixed PXM). Cable Braid Termination option supplied with part codes suffixed /SN or available separately (part code PXM7090) - Choice of cable acceptance 5mm-15mm diameter depending on part code (see data for details) - PXP7088 Series Gland Packs available separately to accomodate all sizes - PXP7082/PXM7082 Sealing Cap available separately to maintain IP rating of unmated connectors - Mate with PXP7010/PXM7010 Series Flex Connectors

// General Information:	
Product Display Title:	Inline Cable Connectors
Product Family:	Circular Power Connectors
Product Series:	7000 Series Buccaneer
Approvals:	UL
Body Material:	Zinc Alloy - Nickel Plated
Body Material Type:	Metal Body With Braid Termination
Contact Type:	Socket Contact
Coupling Type:	Bayonet Lock
Current Max:	25A
Diameter Over Coupling Ring Mm:	42mm
Flamability Rating:	UL94V-0
Function:	Inline Cable Connector
Ip Rating:	IP66
Max Cable Entry Size:	13mm
Min Cable Entry Size:	11mm
Max Contact Accomodation Awg:	10AWG
Min Contact Accomodation Awg:	10AWG
Max Contact Accomodation Mm2:	6mm2
Min Contact Accomodation Mm2:	6mm2
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	2 Contacts
Voltage Max:	600V

// Product PDF Links

7000 Series power connectors...

7000 Series metal body power...

// Product 3D CAD Model Links

PXM7011/02S/ST/1113/SN3D CAD Model