

Impact Wrench Brushless LXT® DTW1004

18V, 1/2", 1 050 Nm, 0 – 2 400 min⁻¹

Model DTW1004 is a cordless impact wrench powered by 18V LXT® Li-Ion battery

Feature and Benefits: Driving Shank 1/2" (12.7mm) Square, pin-detent, 3 stage impact power selection, Reverse switch, Twin LED, Variable speed control by trigger, Electric brake, BL motor.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	170 / 250 / 1050 Nm
No load speed	0 - 900 / 1000 / 2000 min ⁻¹
Impacts per Minute (IPM)	0 - 1800 / 2000 / 2400 min ⁻¹
Drive Square	1/2 "
Tightening Capacity Standard Bolt	M12 - M30
Tightening Capacity High Tensile Bolt	M16 - M24
Sound Power Level (L _{WA})	106 dB(A)
Sound Pressure Level (L _{pA})	98 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,1 - 3,4 kg
Product Dimensions (L x W x H):	261 x 99 x 254 mm

User benefits

- Brushless maintenance-free and long-life motor
- LED light illuminates the work site
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.dk



Related products

Other

User manual

Parts drawing