

5MXTXCL25

Product # # 4656-0107

MXT™ was designed to address our customers' evolving application challenges. Using materials science and process innovation, combined with a patent-pending construction, Gates now offers a new hydraulic solution that is lighter, stronger, and more flexible. Made with strong, high-performance reinforcement and high quality, abrasion-resistant rubber, MXT™ is a universally applicable premium product offering performance above industry standards.

- Tested to 600,000 impulse cycles, 3 times the industry standards.
- More flexible with up to 40% lower force-to-bend for faster and more ergonomic installation.
- Multi-purpose solution meets SAE 100R16, ISO 11237 R16 and EN857 2SC performance standards.



The product images shown are illustrative only and may not be an exact representation of the product.

SPECIFICATIONS

FEATURES

RESOURCES

[Expand All](#) / [Collapse All](#)

PRODUCT DETAILS			
Product #	4656-0107	Description:	5MXTxCL25
Minimum Bend Radius (in)	1.8	Minimum Bend Radius (mm)	45
Min. Burst Pressure (psi)	22000	Hose Inside Diameter (in)	0.31
Hose Inside Diameter (mm)	7.9	Hose Outside Diameter (in)	6
Hose Outside Diameter (mm)	15.2	Inside Diameter (in)	0.31
Inside Diameter (mm)	7.9	Temperature Range	-40°C to +100°C (-40°F to +212°F)
Max. Working Pressure (Bar)	380	Length (m)	25
Outside Diameter (in)	6	Outside Diameter (mm)	15.2
APPLICATION			
Coupling Recommendation	MegaCrimp® Couplings [G25 Series]		
CONSTRUCTION			
Color	Black	Reinforcement	High-tensile steel wire braid
Construction: Cover	Standard Cover. Nitrile, PVC Synthetic Rubber.	Construction: Tube	Nitrile. Hyd Fluids, Phosphate Esters, Water Glycol.
PACKAGING DETAILS			
Weight (lbs.)	0.36		