

SF-7ES1N8A8LB2X - Cable connector



1241941

<https://www.phoenixcontact.com/in/products/1241941>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, straight long, Screw locking mechanism, M23, number of positions: 4+3+PE, contact connection type: Socket, shielded: yes, degree of protection: IP67, cable diameter range: 12 mm ... 15 mm, number of positions: 8, connection method: Crimp connection, series: SF, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly
- Flexible use: reliably connect various cable diameters
- Molded designs with preassembled cables on one or both sides

Commercial data

Item number	1241941
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRBFA
GTIN	4063151397357
Weight per piece (including packing)	137 g
Weight per piece (excluding packing)	126 g
Customs tariff number	85366990
Country of origin	DE

SF-7ES1N8A8LB2X - Cable connector



1241941

<https://www.phoenixcontact.com/in/products/1241941>

Technical data

Notes

Order information:	Order crimp contacts 4 x Ø 1 mm, 4 x Ø 2 mm separately
Safety note	
Safety note	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none">• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.• The products are suitable for applications in plant, controller, and electrical device engineering.• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.• Assembled products may not be manipulated or improperly opened.• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).• When using the product in direct connection with third-party manufacturers, the user is responsible.• For operating voltages > 50 V AC, conductive connector housings must be grounded• Ensure that the protective or functional ground has been properly connected.• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector• Only use tools recommended by Phoenix Contact• The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.• Operate the connector only when it is fully plugged in and interlocked.• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.• Observe the minimum bending radius of the cable. Lay the cable without twisting it.• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting

SF-7ES1N8A8LB2X - Cable connector



1241941

<https://www.phoenixcontact.com/in/products/1241941>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type	Circular connector (cable-side)
Series	SF
Application	Power
Number of positions	8
Connection profile	4+3+PE
Shielded	yes
Coding	N
Thread type	M23

Material specifications

Seal material	FPM
Housing material	Metal

Connection data

Conductor connection

Connection method	Crimp connection
-------------------	------------------

Electrical properties

Contact

Contact diameter	2 mm
Max. current	30 A
Nominal voltage U_N	630 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	6 kV

Contact

Contact diameter	1 mm
Max. current	9 A
Nominal voltage U_N	250 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	4 kV

Connector

Type	straight long
------	---------------

Connection 1

Head design	Socket
Head cable outlet	straight, long
Head thread type	M23

SF-7ES1N8A8LB2X - Cable connector



1241941

<https://www.phoenixcontact.com/in/products/1241941>

Cable/line

External cable diameter	12 mm ... 15 mm
-------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Altitude	3000 m
Permissible humidity (storage/transport)	50 % ... 65 %


SF-7ES1N8A8LB2X - Cable connector

1241941

<https://www.phoenixcontact.com/in/products/1241941>


Drawings

Schematic diagram



Connector pin assignment

Dimensional drawing




Dimensional drawing

SF-7ES1N8A8LB2X - Cable connector



1241941

<https://www.phoenixcontact.com/in/products/1241941>



I = current strength, T = ambient temperature

SF-7ES1N8A8LB2X - Cable connector



1241941

<https://www.phoenixcontact.com/in/products/1241941>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1241941>

cUL Recognized Approval ID: E153698-20041116				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	18 A	12	-

UL Recognized Approval ID: E153698-20041116				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	27 A	12	-

cULus Recognized				
------------------	--	--	--	--

SF-7ES1N8A8LB2X - Cable connector



1241941

<https://www.phoenixcontact.com/in/products/1241941>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

SF-7ES1N8A8LB2X - Cable connector



1241941

<https://www.phoenixcontact.com/in/products/1241941>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

SF-7ES1N8A8LB2X - Cable connector



1241941

<https://www.phoenixcontact.com/in/products/1241941>

Accessories

SF-20KS0,06-1,00 - Crimp contact

1241952

<https://www.phoenixcontact.com/in/products/1241952>



Crimp contact, Socket, turned, Single contact, contact diameter: 2 mm, crimp range: 0.06 mm² ... 1 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

SF-20KS0,25-2,50 - Crimp contact

1237431

<https://www.phoenixcontact.com/in/products/1237431>



Crimp contact, Socket, turned, Single contact, contact diameter: 2 mm, crimp range: 0.25 mm² ... 2.5 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

SF-7ES1N8A8LB2X - Cable connector

1241941

<https://www.phoenixcontact.com/in/products/1241941>



SF-20KS1,50-4,00 - Crimp contact

1241949

<https://www.phoenixcontact.com/in/products/1241949>



Crimp contact, Socket, turned, Single contact, contact diameter: 2 mm, crimp range: 1.5 mm² ... 4 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

SF-10KS0,06-1,00 - Crimp contact

1241922

<https://www.phoenixcontact.com/in/products/1241922>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.06 mm² ... 1 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

SF-7ES1N8A8LB2X - Cable connector

1241941

<https://www.phoenixcontact.com/in/products/1241941>



SF-10KS0,50-1,50 - Crimp contact

1241923

<https://www.phoenixcontact.com/in/products/1241923>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.5 mm² ... 1.5 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>



Torque screwdriver, series: RC, UC, SH, SF

SF-7ES1N8A8LB2X - Cable connector

1241941

<https://www.phoenixcontact.com/in/products/1241941>



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>



Hook wrench, series: RC, UC, RF, SF

SF-Z0068X - Square mounting flange

1244326

<https://www.phoenixcontact.com/in/products/1244326>



Square mounting flange, 4xM3, flange dimensions: 38 mm x 38 mm, series: SF, SH, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

SF-7ES1N8A8LB2X - Cable connector

1241941

<https://www.phoenixcontact.com/in/products/1241941>



PROT-M23-PW-IT-IP20 - Plastic protective cap

1577207

<https://www.phoenixcontact.com/in/products/1577207>

Plastic protective cap, M23, series: SH, SF



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in