

4GBJ4005 thru 4GBJ410


GLASS PASSIVATED BRIDGE RECTIFIERS

REVERSE VOLTAGE FORWARD CURRENT

50 to 1000 Volts4.0 Amperes

FEATURES

- Surge overload rating -135 amperes peak
- Ideal for printed circuit board
- Reliable low cost construction utilizing molded plastic technique
- The plastic material has UL flammability classification 94V-0
- Mounting postition: Any



Dimensions in inches and (milimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25 ℃ ambient temperature unless otherwise specified.

Single phase, half wave ,60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

For capacitive load, derate current by 20%									
CHARACTERISTICS	SYMBOL	4GBJ 4005	4GBJ 401	4GBJ 402	4GBJ 404	4GBJ 406	4GBJ 408	4GBJ 410	UNIT
Maximum Recurrent Peak Reverse Voltage	VRRM	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	VRMS	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	VDC	50	100	200	400	600	800	1000	V
Maximum Average Forward (with heatsink Note 2) Rectified Current @ Tc=100℃ (without heatsink)	l(AV)	4.0 2.4							Α
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC Method)	lғsм	135							Α
Maximum Forward Voltage at 2.0A DC	VF	1.0							V
Maximum Forward Voltage at 4.0A DC	VF	1.1							V
Maximum DC Reverse Current @ TJ=25℃ at Rated DC Blocking Voltage @ TJ=125℃	lr	10.0 500							μA
I ² t Rating for Fusing (t<8.3ms)	I ² t	75.63							A ² s
Typical Junction Capacitance Per Element (Note1)	Сı	45							pF
Typical Thermal Resistance	Rejc	2.2							°C/W
Operating Temperature Range	TJ	-55 to +150							$^{\circ}\!\mathbb{C}$
Storage Temperature Range	Тѕтс	-55 to +150							$^{\circ}$


NOTES: 1.Measured at 1.0MHz and applied reverse voltage of 4.0V DC.


- 2.Device mounted on 50mm*50mm*1.6mm Cu plate heatsink.
- 3.The typical data above is for reference only(典型值仅供参考).


REV. 6, 30-Dec-2014


RATING AND CHARACTERTIC CURVES 4GBJ4005 thru 4GBJ410














The cruve graph is for reference only, can't be the basis for judgment(曲线图仅供参考)!

REV. 6, 30-Dec-2014