

Rittal – The System.

Faster – better – everywhere.

Fibre-optic splicing box, depth-variable – DK 7241.005

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Fibre-optic splicing box, depth-variable – DK 7241.005

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Description: The 482.6 mm (19") splicing box is designed to accommodate splicing cassettes and can be installed in any network distributor with 482.6 mm (19") accommodation and used as a fibre-optic termination or distributor. The variable cassette fixture permits twist-proof installation of all standard splicing cassettes. The rear section of the splicing box is completely open for cable entry, a rubber cable clamp strip provides protection against dust. The fibre-optic cables can be secured with cable ties or cable clamps. The splicing box is infinitely depth-adjustable up to 100 mm within the 482.6 mm (19") flanges. In addition, the splicing box may be fully withdrawn from the 482.6 mm (19") flanges. Two strain relief clips and cable routing clips for the fibre stock provide a solution to suit any fibre-optic wiring system.

Material: Sheet steel

Colour: RAL 7035

Supply includes: Splicing box
Cable routing clips
Cassette cover
Mounting accessories for patch panel

Note: Supplied without patch panels and splicing cassettes

Product description

Units: 1 U

Installation dimensions: Installation depth: 302 mm

Number of splicing cassettes (max.): 2

Packs of: 1 pc(s).

Weight/pack:	3.36 kg
Copper weight (kg per piece):	0
EAN:	4028177167049
Customs tariff number:	94032080
ETIM 7.0:	EC001130
ETIM 6.0:	EC001130
eCl@ss 8.0/8.1:	19170113
eCl@ss 6.0/6.1:	19170107
Product description:	DK Fibre-optic splicing box, 1 U, For D: 302 mm, without pull-out, depth-variable
Approvals	
Certificates:	NA