

Article No. : 6SL3230-1YE10-0UP0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :



Figure similar

### Rated data

#### Input

|                      |                           |                 |
|----------------------|---------------------------|-----------------|
| Number of phases     | 3 AC                      |                 |
| Line voltage         | 380 ... 480 V +10 % -20 % |                 |
| Line frequency       | 47 ... 63 Hz              |                 |
| <b>Rated voltage</b> | <b>400V IEC</b>           | <b>480V NEC</b> |
| Rated current (LO)   | 2.10 A                    | 2.00 A          |
| Rated current (HO)   | 1.70 A                    | 1.60 A          |

#### Output

|                                     |                 |                               |
|-------------------------------------|-----------------|-------------------------------|
| Number of phases                    | 3 AC            |                               |
| <b>Rated voltage</b>                | <b>400V IEC</b> | <b>480V NEC <sup>1)</sup></b> |
| Rated power (LO)                    | 0.75 kW         | 1.00 hp                       |
| Rated power (HO)                    | 0.55 kW         | 0.75 hp                       |
| Rated current (LO)                  | 2.20 A          | 2.10 A                        |
| Rated current (HO)                  | 1.70 A          | 1.60 A                        |
| Rated current (IN)                  | 2.30 A          |                               |
| Max. output current                 | 2.70 A          |                               |
| Pulse frequency                     | 4 kHz           |                               |
| Output frequency for vector control | 0 ... 200 Hz    |                               |
| Output frequency for V/f control    | 0 ... 550 Hz    |                               |

#### Overload capability

|                                                                |  |
|----------------------------------------------------------------|--|
| Low Overload (LO)                                              |  |
| 110% base load current IL for 60 s in a 300 s cycle time       |  |
| High Overload (HO)                                             |  |
| 150% x base load current IH for 60 s within a 600 s cycle time |  |

### General tech. specifications

|                                   |                                           |
|-----------------------------------|-------------------------------------------|
| Power factor $\lambda$            | 0.70 ... 0.85                             |
| Offset factor $\cos \phi$         | 0.96                                      |
| Efficiency $\eta$                 | 0.96                                      |
| Sound pressure level (1m)         | 55 dB                                     |
| Power loss <sup>3)</sup>          | 0.043 kW                                  |
| Filter class (integrated)         | Unfiltered                                |
| EMC category (with accessories)   | without                                   |
| Safety function "Safe Torque Off" | without SIRIUS device (e.g. via S7-1500F) |

### Communication

|               |             |
|---------------|-------------|
| Communication | PROFIBUS DP |
|---------------|-------------|

### Inputs / outputs

#### Standard digital inputs

|                        |       |
|------------------------|-------|
| Number                 | 6     |
| Switching level: 0 → 1 | 11 V  |
| Switching level: 1 → 0 | 5 V   |
| Max. inrush current    | 15 mA |

#### Fail-safe digital inputs

|        |   |
|--------|---|
| Number | 1 |
|--------|---|

#### Digital outputs

|                                    |                |
|------------------------------------|----------------|
| Number as relay changeover contact | 2              |
| Output (resistive load)            | DC 30 V, 5.0 A |
| Number as transistor               | 0              |

#### Analog / digital inputs

|            |                        |
|------------|------------------------|
| Number     | 2 (Differential input) |
| Resolution | 10 bit                 |

#### Switching threshold as digital input

|       |       |
|-------|-------|
| 0 → 1 | 4 V   |
| 1 → 0 | 1.6 V |

#### Analog outputs

|        |                         |
|--------|-------------------------|
| Number | 1 (Non-isolated output) |
|--------|-------------------------|

#### PTC/ KTY interface

|                                                                                                                |
|----------------------------------------------------------------------------------------------------------------|
| 1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5$ °C |
|----------------------------------------------------------------------------------------------------------------|

### Closed-loop control techniques


|                                           |     |
|-------------------------------------------|-----|
| V/f linear / square-law / parameterizable | Yes |
| V/f with flux current control (FCC)       | Yes |
| V/f ECO linear / square-law               | Yes |
| Sensorless vector control                 | Yes |
| Vector control, with sensor               | No  |
| Encoderless torque control                | No  |
| Torque control, with encoder              | No  |

Article No. : 6SL3230-1YE10-0UP0

| Ambient conditions          |                                                                |
|-----------------------------|----------------------------------------------------------------|
| Standard board coating type | Class 3C3, according to IEC 60721-3-3: 2002                    |
| Cooling                     | Air cooling using an integrated fan                            |
| Cooling air requirement     | 0.005 m³/s (0.177 ft³/s)                                       |
| Installation altitude       | 1,000 m (3,280.84 ft)                                          |
| Ambient temperature         |                                                                |
| Operation                   | -20 ... 45 °C (-4 ... 113 °F)                                  |
| Transport                   | -40 ... 70 °C (-40 ... 158 °F)                                 |
| Storage                     | -25 ... 55 °C (-13 ... 131 °F)                                 |
| Relative humidity           |                                                                |
| Max. operation              | 95 % At 40 °C (104 °F), condensation and icing not permissible |

| Connections                    |                                       |
|--------------------------------|---------------------------------------|
| Signal cable                   |                                       |
| Conductor cross-section        | 0.15 ... 1.50 mm² (AWG 24 ... AWG 16) |
| Line side                      |                                       |
| Version                        | screw-type terminal                   |
| Conductor cross-section        | 1.50 ... 2.50 mm² (AWG 16 ... AWG 14) |
| Motor end                      |                                       |
| Version                        | Screw-type terminals                  |
| Conductor cross-section        | 1.50 ... 2.50 mm² (AWG 16 ... AWG 14) |
| DC link (for braking resistor) |                                       |
| PE connection                  | On housing with M4 screw              |
| Max. motor cable length        |                                       |
| Shielded                       | 150 m (492.13 ft)                     |
| Unshielded                     | 300 m (984.25 ft)                     |

| Mechanical data                                      |                                                             |
|------------------------------------------------------|-------------------------------------------------------------|
| Degree of protection                                 | IP20 / UL open type                                         |
| Frame size                                           | FSA                                                         |
| Net weight                                           | 3.2 kg (7.05 lb)                                            |
| Dimensions                                           |                                                             |
| Width                                                | 73 mm (2.87 in)                                             |
| Height                                               | 232 mm (9.13 in)                                            |
| Depth                                                | 218 mm (8.58 in)                                            |
| Standards                                            |                                                             |
| Compliance with standards                            | UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH        |
| CE marking                                           | EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC |
| Converter losses to IEC61800-9-2*                    |                                                             |
| Efficiency class                                     | IE2                                                         |
| Comparison with the reference converter (90% / 100%) | 29.5 %                                                      |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*calculated values

<sup>1)</sup> The output current and HP ratings are valid for the voltage range 440V-480V  
<sup>3)</sup> Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.